


## REVISIONS

| P | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|---|-----|---------------------------|-----------|-----|------|
|   | B2  | REVISED PER ECR-23-170828 | 30MAR2023 | IT  | WH   |
|   |     |                           |           |     |      |
|   |     |                           |           |     |      |
|   |     |                           |           |     |      |




1 FINISH:  
ZnNi 2  $\mu$ m MIN, PASSIVATION BLACK, CHROMIUM IV FREE  
(COMPLIANT TO RoHS)

2 RECOMMENDED TORQUE 0.6Nm  $\pm$ 0.1Nm

-2 AS SHOWN  
WIE GEZEICHNET

© 2023 TE Connectivity. All Rights Reserved.

|                                                                                    |                         |           |                                                                                                      |           |            |               |
|------------------------------------------------------------------------------------|-------------------------|-----------|------------------------------------------------------------------------------------------------------|-----------|------------|---------------|
| DIMENSIONS:                                                                        | DWN<br>G.ACKERMANN      | 29AUG2007 | MATERIAL                                                                                             | STEEL     | FINISH     | 1 -           |
| mm                                                                                 | CHK<br>N.GEISTER        | 03SEP2007 |  TE Connectivity |           |            |               |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:                                          | APVD<br>M.SCHAARSCHMIDT | 03SEP2007 |                                                                                                      |           |            |               |
| 0 PLC $\pm$ 0.15                                                                   | PRODUCT SPEC            | -         | NAME<br>HD20 JACK SCREW<br>FULL METAL TYPE                                                           |           |            |               |
| 1 PLC $\pm$ 0.15                                                                   | APPLICATION SPEC        | -         |                                                                                                      |           |            |               |
| 2 PLC $\pm$ 0.15                                                                   | WEIGHT                  | -         | SIZE                                                                                                 | CAGE CODE | DRAWING NO | RESTRICTED TO |
| 3 PLC $\pm$                                                                        |                         |           | A 4                                                                                                  | 00779     | C-1987198  | -             |
| 4 PLC $\pm$                                                                        |                         |           |                                                                                                      |           |            |               |
| ANGLES $\pm$ 2°                                                                    |                         |           |                                                                                                      |           |            |               |
|  | CUSTOMER DRAWING        |           |                                                                                                      | SCALE     | 2:1        | SHEET 1 OF 1  |
|                                                                                    |                         |           |                                                                                                      |           |            | REV B2        |