


HOUSING CLAMP NUT INNER SLEEVE WASHER WEDGE	BRASS PER QQ-B-626 COMP. 360	GOLD PLATED PER ASTM-B-488 OVER NICKEL PLATE PER AMS-QQ-N-290 COPPER PLATE PER AMS-2418
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457, MIL-P-19468, AND FED. SPEC L-P-403	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B196, ALLOY 173	GOLD PLATED PER ASTM-B-488 OVER NICKEL PLATE PER AMS-QQ-N-290 COPPER PLATE PER AMS-2418
RETAINING RING	BERYLLIUM COPPER PER ASTM B194	GOLD PLATE PER ASTM-B-488 OVER COPPER PLATE PER AMS-2418
SLEEVE CAP	BRASS PER QQ-B-626 COMP. 360	GOLD PLATE PER ASTM-B-488 OVER COPPER PLATE PER AMS-2418
COMPONENT	MATERIAL	FINISH

1. CAPTURED CENTER CONTACT.



DESIGNED TO USE MIS-20057/5-001 CABLE
CABLE ENTRY DIAMETER MIN
INNER SLEEVE: .065 [1.65]
CONTACT: .028 [0.71]
CLAMP NUT: .112 [2.84]

1996185-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M (ISO STANDARDS)		DWN C.C.THOMAS 06FEB2013	 TE Connectivity								
		CHK D.WILSON 2-6-13									
DIMENSIONS: INCHES [mm]		APVD D.WILSON 2-6-13	NAME SMB RT ANGLE SNAP ON CABLE PLUG ASSY,CLAMP ATTACHMENT								
		PRODUCT SPEC —									
		APPLICATION SPEC 408-4729	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO					
MATERIAL SEE TABLE		WEIGHT —	A2	00779	C=1996185	—					
SEE TABLE SEE TABLE		CUSTOMER DRAWING				SCALE	8:1	SHEET	1 of 1	REV	A