



D


C

B

A



SCALE 6:1



- 1 MATERIAL: SMOOTHBORE SMPM CONNECTOR BODY & CENTER CONTACT - BERYLIUM COPPER, ALLOY UNS C17300 CONDITION TD04, PER ASTM B196. INSULATORS - TEFLON (PTFE) ROD, PER ASTM D 1710. MODULE BODY & OSMC CONNECTORS - STAINLESS STEEL, PER UNS S30300 SLOTTED SPRING PIN - NICKEL STAINLESS STEEL
- 2 FINISH: MODULE BODY, CONNECTOR BODIES & CENTER CONTACT - GOLD PLATE OVER NICKEL SLOTTED SPRING PIN - PASSIVATED
- 3 FINISH: MODULE BODY, OSMC CONNECTOR BODY & SLOTTED SPRING PIN - PASSIVATED SMOOTHBORE SMPM CONNECTOR BODY & CENTER CONTACT - GOLD PLATE OVER NICKEL

3	1996777-2
2	1996777-1
SURFACE FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RJM3 04FEB2011	TE Connectivity	
DIMENSIONS: INCHES		CHK STM 04FEB2011		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD STM 04FEB2011	NAME 8 POSITION P.C.B. MOUNT RF MODULE OSMC CONTACTS VITA 67 BACKPLANE - C'SINK MTG. HOLES	
0 PLC ±.1		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO	
1 PLC ±.01		APPLICATION SPEC	RESTRICTED TO	
2 PLC ±.001		WEIGHT	A100779C=1996777	
3 PLC ±.0005		CUSTOMER DRAWING	SCALE 8:1 SHEET 1 OF 1 REV H	
ANGLES FINISH				
SEE TABLE				