




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL REVISION	18FEB2022	SP	RM



TCPN	TE Product Type (Entretec)	RAL NUMBER	COLOR	UL RATING	CERTIFICATIONS	M EN 60423	TL	H	$\varnothing D$	Sw 1	Sw 2	Clamping Range $\varnothing$ min - max
1SNG618001R0000	EP-RJG-M20-LGR-A	7035	L.Grey	TYPE 4X	cULus	M20x1.5	10.0	31.9	30.9	27+0.00 -0.33	27+0.00 -0.33	3.0 - 6.0
1SNG618002R0000	EP-RJG-M20-GR-A	7001	Grey	TYPE 4X	cULus	M20x1.5	10.0	31.9	30.9	27+0.00 -0.33	27+0.00 -0.33	3.0 - 6.0
1SNG618003R0000	EP-RJG-M20-BL-A	9005	Black	TYPE 4X	cULus	M20x1.5	10.0	31.9	30.9	27+0.00 -0.33	27+0.00 -0.33	3.0 - 6.0
1SNG618004R0000	EP-RJG-M20-LGR-B	7035	L.Grey	TYPE 4X	cULus	M20x1.5	15.0	31.9	30.9	27+0.00 -0.33	27+0.00 -0.33	3.0 - 6.0
1SNG618005R0000	EP-RJG-M20-GR-B	7001	Grey	TYPE 4X	cULus	M20x1.5	15.0	31.9	30.9	27+0.00 -0.33	27+0.00 -0.33	3.0 - 6.0
1SNG618006R0000	EP-RJG-M20-BL-B	9005	Black	TYPE 4X	cULus	M20x1.5	15.0	31.9	30.9	27+0.00 -0.33	27+0.00 -0.33	3.0 - 6.0
1SNG618007R0000	EP-RJG-M25-LGR-A	7035	L.Grey	TYPE 4X	cULus	M25x1.5	8.0	37.7	32.5	29+0.00 -0.33	29+0.00 -0.33	3.0 - 6.0
1SNG618008R0000	EP-RJG-M25-GR-A	7001	Grey	TYPE 4X	cULus	M25x1.5	8.0	37.7	32.5	29+0.00 -0.33	29+0.00 -0.33	3.0 - 6.0
1SNG618009R0000	EP-RJG-M25-BL-A	9005	Black	TYPE 4X	cULus	M25x1.5	8.0	37.7	32.5	29+0.00 -0.33	29+0.00 -0.33	3.0 - 6.0
1SNG618010R0000	EP-RJG-M25-LGR-B	7035	L.Grey	TYPE 4X	cULus	M25x1.5	15.0	37.7	32.5	29+0.00 -0.33	29+0.00 -0.33	3.0 - 6.0
1SNG618011R0000	EP-RJG-M25-GR-B	7001	Grey	TYPE 4X	cULus	M25x1.5	15.0	37.7	32.5	29+0.00 -0.33	29+0.00 -0.33	3.0 - 6.0
1SNG618012R0000	EP-RJG-M25-BL-B	9005	Black	TYPE 4X	cULus	M25x1.5	15.0	37.7	32.5	29+0.00 -0.33	29+0.00 -0.33	3.0 - 6.0
1SNG618013R0000	EP-RJG-M25-LGR-C	7035	L.Grey	TYPE 4X	cULus	M25x1.5	10.0	38.4	37.2	33+0.00 -0.39	33+0.00 -0.39	3.0 - 6.0
1SNG618014R0000	EP-RJG-M25-GR-C	7001	Grey	TYPE 4X	cULus	M25x1.5	10.0	38.4	37.2	33+0.00 -0.39	33+0.00 -0.39	3.0 - 6.0
1SNG618015R0000	EP-RJG-M25-BL-C	9005	Black	TYPE 4X	cULus	M25x1.5	10.0	38.4	37.2	33+0.00 -0.39	33+0.00 -0.39	3.0 - 6.0
1SNG618016R0000	EP-RJG-M25-LGR-D	7035	L.Grey	TYPE 4X	cULus	M25x1.5	15.0	38.4	37.2	33+0.00 -0.39	33+0.00 -0.39	3.0 - 6.0
1SNG618017R0000	EP-RJG-M25-GR-D	7001	Grey	TYPE 4X	cULus	M25x1.5	15.0	38.4	37.2	33+0.00 -0.39	33+0.00 -0.39	3.0 - 6.0
1SNG618018R0000	EP-RJG-M25-BL-D	9005	Black	TYPE 4X	cULus	M25x1.5	15.0	38.4	37.2	33+0.00 -0.39	33+0.00 -0.39	3.0 - 6.0



3	1	CAP	-	PA6 V2 (F1 Listed)	-
2	1	SEAL	-	CR	-
1	1	BODY	-	PA6 V2 (F1 Listed)	-
RPT	QTY	DOC	TITLE	DRAWING NUMBER	MATERIAL
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN: 18FEB2022 CHK: Shindhe, Puneet APVD: Rajan, N. Kasi Rafiq, Mohd	NAME: -	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC: M-RJ45-GLAND-PA	
MATERIAL REF. TABLE		WEIGHT		SIZE: A	
CUSTOMER DRAWING			SCALE: 5:1		SHEET 1 OF 1