




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL REVISION	05MAR2022	SP	RM



TCPN	TE Product Type (Entrelec)	M EN 60423	TL	H	ØD	SW 1	SW 2	ØD1	Clamping Range Ø min. - max.
1SNG619001R0000	EM-RJG-M20-MET-A	M20x1.5	8.0	28.0	26.5	24	24	6.0	3.0-6.0
1SNG619002R0000	EM-RJG-M20-MET-B	M20x1.5	12.0	28.0	26.5	24	24	6.0	3.0-6.0
1SNG619003R0000	EM-RJG-M20-MET-C	M20x1.5	8.0	28.0	26.5	24	24	9.3	5.0-9.0
1SNG619004R0000	EM-RJG-M20-MET-D	M20x1.5	6.0	28.0	26.5	24	24	9.3	5.0-9.0
1SNG619005R0000	EM-RJG-M25-MET-A	M25x1.5	8.0	28.0	30.0	24	27	6.0	3.0-6.0
1SNG619006R0000	EM-RJG-M25-MET-B	M25x1.5	8.0	30.6	30.0	27	27	6.2	3.0-6.0
1SNG619007R0000	EM-RJG-M25-MET-C	M25x1.5	10.0	32.8	33.0	30	30	6.2	3.0-6.0
1SNG619008R0000	EM-RJG-M25-MET-D	M25x1.5	12.0	28.0	30.0	24	27	6.0	3.0-6.0
1SNG619009R0000	EM-RJG-M25-MET-E	M25x1.5	8.0	28.0	30.0	24	27	9.3	5.0-9.0
1SNG619010R0000	EM-RJG-M32-MET-A	M32x1.5	9.0	32.8	37.5	30	34	6.2	3.0-6.0
1SNG619011R0000	EM-RJG-M40-MET-A	M40x1.5	9.0	43.3	48.4	43	43	8.2	5.0-8.0
1SNG619012R0000	EM-RJG-M40-MET-B	M40x1.5	15.0	43.3	48.4	43	43	8.2	5.0-8.0

5	1	O-RING	-	NBR	-
4	1	METAL GLAND CAP	-	BRASS (NICKEL PLATED)	-
3	1	SEAL	-	CR	-
2	1	PLASTIC INSERT	-	PA 6	-
1	1	METAL CABLE BODY	-	BRASS (NICKEL PLATED)	-
RPT	QTY	DOC TITLE	DRAWING NUMBER	MATERIAL	COMMENTS
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 05MAR2022 Shinde, Puneet	TE Connectivity	
			CHK 05MAR2022 Rajan n. Kasi		
			APVD 05MAR2022 Rafeeq. Mohd		
			PRODUCT SPEC M-RJ45-GLAND-BRASS		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME - M-RJ45-GLAND-BRASS	
		0 PLC ±-		M-RJ45-GLAND-BRASS	
		1 PLC ±1			
		2 PLC ±1			
		3 PLC ±1			
		4 PLC ±1			
ANGLES ±		APPLICATION SPEC -		SIZE	
MATERIAL REF, TABLE -		FINISH REF, TABLE -		CAGE CODE	
				DRAWING NO	
				RESTRICTED TO	
				A300779	
				©1SNP061357-0100	
				SCALE 2:1	
				SHEET 1 OF 1	
				REV A	
CUSTOMER DRAWING					