



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL REVISION	05MAR2022	SP	RM



TCPN	TE Product Type (Entrelec)	PG DIN 40430	TL	H	∅D	SW 1	SW 2	∅D1	Clamping Range ∅ min - max
1SNG619013R0000	EM-RJG-PG135-MET-A	PG 13,5	6.5	28.0	26.5	24	24	9.3	5.0-9.0
1SNG619014R0000	EM-RJG-PG16-MET-A	PG 16	6.5	28.0	26.5	24	24	6.0	3.0-6.0
1SNG619015R0000	EM-RJG-PG16-MET-B	PG 16	10.0	28.0	26.5	24	24	6.0	3.0-6.0
1SNG619016R0000	EM-RJG-PG21-MET-A	PG 21	7.2	32.8	33.0	30	30	9.3	5.0-9.0
1SNG619017R0000	EM-RJG-PG21-MET-B	PG 21	12.0	32.8	33.0	30	30	6.2	3.0-6.0



5	1	O-RING	-	NBR	-
4	1	METAL GLAND CAP	-	BRASS (NICKEL PLATED)	-
3	1	SEAL	-	CR	-
2	1	PLASTIC INSERT	-	PA 6	-
1	1	METAL CABLE BODY	-	BRASS (NICKEL PLATED)	-
RPT	QTY	DOC TITLE	DRAWING NUMBER	MATERIAL	COMMENTS
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 05MAR2022 Shindhe, Puneet	TE Connectivity	
			CHK 05MAR2022 Rajan n. Kasi		
			APVD 05MAR2022 Rafeeq. Mohd		
			PRODUCT SPEC PG-RJ45-GLAND-BRASS		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME -	
		0 PLC ±-		PG-RJ45-GLAND-BRASS	
		1 PLC ±1		SIZE	
		2 PLC ±1		CAGE CODE	
		3 PLC ±1		DRAWING NO	
		4 PLC ±1		RESTRICTED TO	
		ANGLES ±		A3 00779 ©1SNP061358-0100	
MATERIAL REF, TABLE		FINISH REF, TABLE		WEIGHT -	
				CUSTOMER DRAWING	
				SCALE 2:1	SHEET 1 OF 1
				REV A	