




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL REVISION	22MAR2022	GN	RM

SECTION A-A



TCPN	TE Product Type (Entrelec)	NPT ANSI B1.20.1	TL	H	ØD	SW 1	SW 2	Clamping Range Ø min - max	Shield Diameter Ø min-max mm
1SNG614011R0000	EM-EMC 4-NPT14-MET-A	NPT 1/4"	11.5	28.1	16.5	14	15	3.0 - 6.5	2.0 - 5.0
1SNG614012R0000	EM-EMC 4-NPT38-MET-A	NPT 3/8"	11.5	33.8	22.0	20	20	5.0 - 10.0	3.5 - 8.0
1SNG614013R0000	EM-EMC 4-NPT12-MET-A	NPT 1/2"	15.0	37.7	24.5	22	22	6.0 - 12.0	4.5 - 10.0
1SNG614014R0000	EM-EMC 4-NPT12-MET-B	NPT 1/2"	15.0	39.7	26.8	24	24	7.5 - 14.0	5.5 - 11.5
1SNG614015R0000	EM-EMC 4-NPT34-MET-A	NPT 3/4"	15.0	42.7	33.0	30	30	10.0 - 18.0	7.0 - 14.0
1SNG614016R0000	EM-EMC 4-NPT1-MET-A	NPT 1"	20.0	52.1	44.5	40	40	16.0 - 25.0	12.0 - 20.0
1SNG614017R0000	EM-EMC 4-NPT114-MET-A	NPT 1 1/4"	20.0	61.0	55.5	50	50	22.0 - 32.0	18.0 - 27.0
1SNG614018R0000	EM-EMC 4-NPT112-MET-A	NPT 1 1/2"	22.0	71.0	64.0	58	58	30.0 - 38.0	26.0 - 34.0
1SNG614019R0000	EM-EMC 4-NPT2-MET-A	NPT 2"	22.0	71.0	75.0	64	68	34.0 - 44.0	30.0 - 40.0

6	1	GLAND CAP	-	Brass (Nickel plated)	-			
5	1	SEAL	-	CR	-			
4	1	PLASTIC INSERT	-	PA6 V2	-			
3	1	EMC PRESSURE RING	-	Brass (Nickel plated)	-			
2	1	EMC SPRING	-	CuBe (Tin Plated)	-			
1	1	EMC CABLE GLAND BODY	-	Brass (Nickel plated)	-			
RPT	QTY	DOC TITLE	DRAWING NUMBER	MATERIAL	COMMENTS			
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 22MAR2022 N Hunashikatti, Girish	TE Connectivity				
			CHK 22MAR2022 Rajan n. Kasi					
			APVD 22MAR2022 Rafeeq. Mohd					
			PRODUCT SPEC NPT-EMC 4-GLAND					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±1 1 PLC ±1 2 PLC ±1 3 PLC ±1 4 PLC ±1 ANGLES ±	NAME	NPT-EMC 4-GLAND				
			APPLICATION SPEC	-				
			-					
			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL REF, TABLE -		FINISH REF, TABLE -	WEIGHT -	A3	00779	©=1SNP061365-0100	-	
CUSTOMER DRAWING						SCALE 2:1	SHEET 1 OF 1	REV A1