




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	REVISED AS PER ECR-24-219489	04SEP2024	GH	CS

SECTION A-A



TCPN	TE Product Type (Entrelec)	PG DIN 40430	TL	H	ØD	SW 1	SW 2	Clamping Range Ø min - max	Shield Diameter Ø min-max mm
1SNG614020R0000	EM-EMC 4-PG7-MET-A	PG 7	6.0	28.1	16.5	14	15	3.0 - 6.5	2.0 - 5.0
1SNG614021R0000	EM-EMC 4-PG9-MET-A	PG 9	6.0	33.8	18.9	17	17	4.0 - 8.0	2.5 - 6.0
1SNG614022R0000	EM-EMC 4-PG11-MET-A	PG 11	6.0	33.1	23.0	20	21	5.0 - 10.0	3.5 - 8.0
1SNG614023R0000	EM-EMC 4-PG135-MET-A	PG 13.5	6.5	31.7	24.5	22	22	6.0 - 12.0	4.5 - 10.0
1SNG614024R0000	EM-EMC 4-PG16-MET-A	PG 16	6.5	39.7	27.5	24	25	7.5 - 14.0	5.5 - 11.5
1SNG614025R0000	EM-EMC 4-PG21-MET-A	PG 21	7.0	42.7	35.5	30	32	10.0 - 18.0	7.0 - 14.0
1SNG614026R0000	EM-EMC 4-PG29-MET-A	PG 29	9.0	52.9	44.5	40	40	16.0 - 25.0	12.0 - 20.0
1SNG614027R0000	EM-EMC 4-PG36-MET-A	PG 36	9.0	60.0	55.5	50	50	22.0 - 32.0	18.0 - 27.0
1SNG614028R0000	EM-EMC 4-PG42-MET-A	PG 42	12.0	72.4	66.5	58	60	30.0 - 38.0	26.0 - 34.0
1SNG614029R0000	EM-EMC 4-PG48-MET-A	PG 48	14.0	58.5	75.0	64	68	34.0 - 44.0	30.0 - 40.0



NBR	1	O-RING	7
Brass (Nickel plated)	1	GLANDS CAP	6
CR	1	SEAL	5
PA6 V2	1	PLASTIC INSERT	4
Brass (Nickel plated)	1	EMC PRESSURE RING	3
CuBe (Tin Plated)	1	EMC SPRING	2
Brass (Nickel plated)	1	EMC CABLE GLAND BODY	1
MATERIAL	QTY	DESCRIPTION	ITEM NO.
la quantite indiquée peut correspondre à une unité particulière: voir : Observations (par colisage, longueur...) The quantity indicated may refer to a particular unit, see remarks (package, length...)			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22MAR2022 N Hunashikatti, Girish	 TE Connectivity	
DIMENSIONS: mm		CHK 22MAR2022 Rajan n. Kasi		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 22MAR2022 Rafeeq. Mohd	NAME PG-EMC 4-GLAND	
0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.1 3 PLC ±0.1 4 PLC ±0.1 ANGLES ±0.1		PRODUCT SPEC PG-EMC 4-GLAND	SIZE A3	
MATERIAL REF. TABLE		APPLICATION SPEC	CAGE CODE 00779	
FINISH REF. TABLE		WEIGHT	DRAWING NO C=1SNP061366-0100	
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	
			REV A2	