






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL REVISION	26MAR2022	KR	RM

Single Seal
SECTION A-A




Double Seal
SECTION A-A



8	1	GLAND CAP EURO	-	Brass (Nickel plated)	-
7	1	INNER SEAL EURO	-	CR	-
6	1	SEAL EURO	-	CR	-
5	1	PLASTIC INSERT EURO	-	PA 6	-
4	1	PUSH AND TIGHTEN METAL UPPER BODY	-	Brass (Nickel plated)	-
3	1	PLUG IN WASHER WITH CLAWS NATURAL	-	PA 66	-
2	1	PLUG IN FRICTION WASHER	-	CR	-
1	1	PLUG IN LOWER BODY	-	PA 66	-
RPT	QTY	DOC TITLE	DRAWING NUMBER	MATERIAL	COMMENTS
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 26MAR2022 CHK Rajan, M. Kas APVD Rafeeq, Mohd Rafeeq, Mohd 26MAR2022	NAME - TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME SNAP-IN-GLAND-BRASS	
mm		0 PLC ±.1 1 PLC ±.1 2 PLC ±.1 3 PLC ±.1 4 PLC ±.1 ANGLES ±.1	APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL REF. TABLE		FINISH -	WEIGHT -	A 00779 ©=1SNP061374-0100	
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 2	REV A1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL REVISION	26MAR2022	KR	RM

TCPN	TE Product Type (Entrelec)	Snap Size ϕ	Seal Type	ϕD	ϕSD	ϕA	SL	H	E	SW 1 Cap	SW 2 Body	Clamping Range ϕ min-max	Clamping Range (S1) (Outer Seal)	Clamping Range (S1+S2) (Outer Seal+Inner Seal)
1SNG623001R0000	EM-SIG-SZ16-MET-A	16.0	Single	28.3	15.9	26.5	9.0	44.9	0.5 - 4.0	20	20	3.0 - 7.0	5.0 - 10.0	-
1SNG623002R0000	EM-SIG-SZ16-MET-B	16.0	Single	28.3	15.9	26.5	9.0	44.9	0.5 - 4.0	20	20	5.0 - 10.0	5.0 - 10.0	-
1SNG623003R0000	EM-SIG-SZ16-MET-C	16.0	Double	28.3	15.9	26.5	9.0	45.5	0.5 - 4.0	20	20	3.0 - 10.0	5.0 - 10.0	3.0 - 7.0
1SNG623004R0000	EM-SIG-SZ20-MET-A	20.0	Single	32.3	19.9	30.3	9.0	43.8	0.5 - 4.0	22	22	5.0 - 9.0	6.0 - 12.0	-
1SNG623005R0000	EM-SIG-SZ20-MET-B	20.0	Single	32.3	19.9	30.3	9.0	43.8	0.5 - 4.0	22	22	6.0 - 12.0	6.0 - 12.0	-
1SNG623006R0000	EM-SIG-SZ20-MET-C	20.0	Double	32.3	19.9	30.3	9.0	44.5	0.5 - 4.0	22	22	5.0 - 12.0	6.0 - 12.0	5.0 - 8.5
1SNG623007R0000	EM-SIG-SZ25-MET-A	25.0	Single	38.5	24.9	36.3	9.0	47.0	0.5 - 4.0	27	27	9.0 - 13.0	11.0 - 17.0	
1SNG623008R0000	EM-SIG-SZ25-MET-B	25.0	Single	38.5	24.9	36.3	9.0	46.4	0.5 - 4.0	27	27	11.0 - 17.0	11.0 - 17.0	
1SNG623009R0000	EM-SIG-SZ25-MET-C	25.0	Double	38.5	24.9	36.3	9.0	47.3	0.5 - 4.0	27	27	8.0 - 17.0	11.0 - 17.0	8.0 - 13.5
1SNG623010R0000	EM-SIG-SZ32-MET-A	32.0	Single	45.5	31.9	43.2	9.0	54.3	0.5 - 4.0	34	34	11.0 - 15.0	15.0 - 21.0	-
1SNG623011R0000	EM-SIG-SZ32-MET-B	32.0	Single	45.5	31.9	43.2	9.0	54.3	0.5 - 4.0	34	34	15.0 - 21.0	15.0 - 21.0	-
1SNG623012R0000	EM-SIG-SZ32-MET-C	32.0	Double	45.5	31.9	43.2	9.0	54.5	0.5 - 4.0	34	34	11.0 - 21.0	15.0 - 21.0	11.0 - 16.0
1SNG623013R0000	EM-SIG-SZ40-MET-A	40.0	Single	59.0	39.9	56.1	13.2	62.1	0.5 - 4.0	43	43	16.0 - 23.0	19.0 - 28.0	-
1SNG623014R0000	EM-SIG-SZ40-MET-B	40.0	Single	59.0	39.9	56.1	13.2	62.1	0.5 - 4.0	43	43	19.0 - 28.0	19.0 - 28.0	-
1SNG623015R0000	EM-SIG-SZ40-MET-C	40.0	Double	59.0	39.9	56.1	13.2	63.0	0.5 - 4.0	43	43	16.0 - 28.0	19.0 - 28.0	16.0 - 21.0

8	1	GLAND CAP EURO	-	Brass (Nickel plated)	-
7	1	INNER SEAL EURO	-	CR	-
6	1	SEAL EURO	-	CR	-
5	1	PLASTIC INSERT EURO	-	PA 6	-
4	1	PUSH AND TIGHTEN METAL UPPER BODY	-	Brass (Nickel plated)	-
3	1	PLUG IN WASHER WITH CLAWS NATURAL	-	PA 66	-
2	1	PLUG IN FRICTION WASHER	-	CR	-
1	1	PLUG IN LOWER BODY	-	PA 66	-
RPT	QTY	DOC TITLE	DRAWING NUMBER	MATERIAL	COMMENTS
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: Rajan, M. Kas CHK: Rafeeq, Mohd APVD: Rafeeq, Mohd	26MAR2022	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.1 1 PLC ±.1 2 PLC ±.1 3 PLC ±.1 4 PLC ±.1 ANGLES ±.1 FINISH -	NAME: SNAP-IN-GLAND-BRASS	SIZE: CAGE CODE: DRAWING NO: RESTRICTED TO:	
		PRODUCT SPEC: SNAP-IN-GLAND-BRASS APPLICATION SPEC: -	00779	©=1SNP061374-0100	
MATERIAL REF. TABLE		WEIGHT: -	CUSTOMER DRAWING		
			SCALE: 4:1	SHEET: 2 OF 2	REV: A1