

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	Drawing creation	29MAR2021		



Cross Section (mm ²)	Cross Section (AWG)	Part Number	Type	Color	A	B	C	D
0,34	22	ISET1111001R0000	WF003-08-GN	Green	12,0	8,0	0,8	2,0
		ISET1111026R0000	WF003-08-TR	Turquoise	12,0	8,0	0,8	2,0
0,50	20	ISET1111002R0000	WF005-08-WH	White	14,0	8,0	1,0	2,6
0,75	18	ISET1111003R0000	WF007-08-BL	Blue	14,0	8,0	1,2	2,8
		ISET1111004R0000	WF007-12-BL	Blue	18,0	12,0	1,2	2,8
		ISET1111027R0000	WF007-08-GR	Grey	14,0	8,0	1,2	2,8
		ISET1111028R0000	WF007-12-GR	Grey	18,0	12,0	1,2	2,8
1	17	ISET1111005R0000	WF010-08-RD	Red	14,0	8,0	1,4	3,0
		ISET1111006R0000	WF010-12-RD	Red	18,0	12,0	1,4	3,0
1,5	16	ISET1111007R0000	WF015-08-BK	Black	14,0	8,0	1,7	3,5
		ISET1111008R0000	WF015-12-BK	Black	18,0	12,0	1,7	3,5
		ISET1111009R0000	WF015-18-BK	Black	24,0	18,0	1,7	3,5
2,5	14	ISET1111010R0000	WF025-08-GR	Grey	14,0	8,0	2,2	4,2
		ISET1111011R0000	WF025-12-GR	Grey	18,0	12,0	2,2	4,2
		ISET1111012R0000	WF025-18-GR	Grey	24,0	18,0	2,2	4,2
		ISET1111029R0000	WF025-08-BL	Blue	14,0	8,0	2,2	4,2
		ISET1111030R0000	WF025-12-BL	Blue	18,0	12,0	2,2	4,2
		ISET1111031R0000	WF025-18-BL	Blue	24,0	18,0	2,2	4,2

THIS DRAWING IS A CONTROLLED DOCUMENT 09		DWN 11-21 04:00:34 AM Deligny, Charlotte			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:			
		0 PLC ±-		NAME	
		1 PLC ±0.1		INSULATED WIRE END FERRULE - SIMPLE	
MATERIAL		FINISH		PRODUCT SPEC	
-		-		-	
		3 PLC ±0.01		APPLICATION SPEC	
		4 PLC ±0.005		-	
		ANGLES ±-		WEIGHT	
				-	
				SIZE	
				A3	
				CAGE CODE	
				00779	
				DRAWING NO	
				C=1SNP300171-0000	
				RESTRICTED TO	
				-	
				SCALE	
				4:1	
				SHEET	
				1 OF 2	
				REV	
				A4	

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD

Cross Section (mm ²)	Cross Section (AWG)	ENT Part Number	Type	Color	A	B	C	D
4	12	ISET111013R0000	WF040-10-OR	Orange	17,0	10,0	2,8	4,8
		ISET111014R0000	WF040-12-OR	Orange	20,0	12,0	2,8	4,8
		ISET111015R0000	WF040-18-OR	Orange	26,0	18,0	2,8	4,8
		ISET111032R0000	WF040-10-GR	Grey	17,0	10,0	2,8	4,8
		ISET111033R0000	WF040-12-GR	Grey	20,0	12,0	2,8	4,8
		ISET111034R0000	WF040-18-GR	Grey	26,0	18,0	2,8	4,8
6	10	ISET111016R0000	WF060-12-GN	Green	20,0	12,0	3,5	6,3
		ISET111017R0000	WF060-18-GN	Green	26,0	18,0	3,5	6,3
		ISET111035R0000	WF060-12-YL	Yellow	20,0	12,0	3,5	6,3
		ISET111036R0000	WF060-18-YL	Yellow	26,0	18,0	3,5	6,3
10	8	ISET111018R0000	WF100-12-BR	Brown	22,0	12,0	4,5	7,6
		ISET111019R0000	WF100-18-BR	Brown	28,0	18,0	4,5	7,6
		ISET111037R0000	WF100-12-RD	Red	22,0	12,0	4,5	7,6
		ISET111038R0000	WF100-18-RD	Red	28,0	18,0	4,5	7,6
16	6	ISET111020R0000	WF160-12-IV	Ivory	24,0	12,0	5,8	8,8
		ISET111021R0000	WF160-18-IV	Ivory	28,0	18,0	5,8	8,8
		ISET111039R0000	WF160-12-BL	Blue	24,0	12,0	5,8	8,8
		ISET111040R0000	WF160-18-BL	Blue	28,0	18,0	5,8	8,8
25	4	ISET111022R0000	WF250-16-BK	Black	30,0	16,0	7,3	11,2
		ISET111023R0000	WF250-22-BK	Black	36,0	22,0	7,3	11,2
35	2	ISET111024R0000	WF350-16-RD	Red	30,0	16,0	8,3	12,7
50	1	ISET111025R0000	WF500-20-BL	Blue	36,0	20,0	10,3	15,0

THIS DRAWING IS A CONTROLLED DOCUMENT 09		2021-11-21 04:00:34 AM Deligny, Charlotte		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:			
		0 PLC ±-		NAME	
		1 PLC ±0.1		INSULATED WIRE END FERRULE - SIMPLE	
MATERIAL		2 PLC ±0.01		PRODUCT SPEC	
		3 PLC ±0.005		-	
FINISH		4 PLC ±0.0001		APPLICATION SPEC	
		ANGLES ±-		-	
-		-		WEIGHT	
-		-		-	
CUSTOMER DRAWING; RESTRICTED CUSTOMER				SCALE 4:1	SHEET 2 OF 2
SIZE A3				CAGE CODE 00779	DRAWING NO. C-1SNP300171-0000
RESTRICTED TO				-	
REV A4					