





P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL REVISION	29MAY2024	IS	RM






Laser printing
RAL7010

DIN EN 60 715 35x7,5 / 15
/Mounting for DIN EN 60 715
35x7,5 /15 mounting rail

SCALE 3:2

Fuse holder with LED
Laser printing
Pantone Cool grey 3C (RAL7047 telegrey)



B(3:1)

A(3:1)

- Note:
1. No welding visible outside
 2. Printing is smudge- and scratch-proof
 3. The fuse holder must not be welded to the housing (movable)
 4. Any sweat leakage inside is allowed Do not affect device function
 5. Housing RAL 7035 (light grey)
 6. Handle RAL 9005 (black)

1SNF100024R0000
TCPN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 29MAY2024 Irfan sayed	 TE Connectivity	
DIMENSIONS: mm		CHK 05JUN2024 Rafeeq, Mohd		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 05JUN2024 Saurabh Bisht	NAME DL25/18.SFL.1	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC -	SIZE A2	
MATERIAL -		APPLICATION SPEC -	CAGE CODE 00779	
FINISH -		WEIGHT 57g	DRAWING NO C-1SNP300600-0100	
		CUSTOMER DRAWING	RESTRICTED TO -	
		SCALE 3:2	SHEET 1 OF 1	
			REV A1	