

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DS

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

A

RELEASED

06.OCT'11

DG

HG

MOUNTING DIMENSION FOR P.C.B.

SECTION A-A

NOTE.

1. General Tolerance : ± 0.3 , $\pm 3^\circ$
 2. APPLICABLE P.C.B. THICKNESS : 1.6mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

DG JEONG

CHK

KT LIM

APVD

HG CHO

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

NAME

025 20P HEADER ASS'Y FOR PDIM

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=2005358

RESTRICTED TO

-

SCALE

1:1

SHEET

1

OF

1

REV

A

NO.	COLOR	MATERIAL	DESCRIPTION	QT'Y	NAME
4	TIN PLATE	BRASS	025 TAB TERMINAL(SHORT)	10	2005358-2
3	TIN PLATE	BRASS	025 TAB TERMINAL(LONG)	10	2005358-3
2	GRAY	PA6T-GF15	110 10P CAP HSG FOR PDIM GRAY	-	ASSY P/N
1	BLACK	PA6T-GF15	110 10P CAP HSG FOR PDIM BLACK	1	

TE Connectivity

1470-19 (3/11)