


LOC		DIST		REVISIONS			
P	F	ZONE	LTR	DESCRIPTION	DATE	APPD	
DF	BO		G	REV & REDRAWN DF-4297	PY	11-91	DBM
			H	REV PER 0600-4161-95	JB	08-95	DBM



- 1 MATERIAL: PHENOLIC PER MIL-M-14, TYPE CFG OR MFH, COLOR: BLACK
- 2 AMP PART NO, DATE CODE, CSA CERT AND ARROWS MARKED WITH WHITE INK OR BY LASER MARKING AT APPROXIMATE AREA SHOWN, EITHER SIDE
- 3. THIS MODULE ACCEPTS FOUR TYPE XII FEMALE POWER CONTACTS
- 4 WARNING STATEMENT MARKED WITH WHITE INK AT APPROXIMATE AREA SHOWN, ON SIDE OPPOSITE PART NUMBER.

AS SHOWN	202625-2
DESCRIPTION	PART NUMBER

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm]		PART NO	
TOLERANCES ON :		AMP AMP Incorporated Harrisburg, PA 17105-3608	
2 PLC DEC ± -		NAME	
3 PLC DEC ± .005		FEMALE BLOCK	
ANGLES ± -		G SERIES, TYPE XII	
MATERIAL	DR 9-10-91 P.YEAGER	SIZE	CAGE CODE
	CHK 11-12-91 D.B.MUMMEY	C	00779
	APPD 11-12-91 D.B.MUMMEY	SCALE	DRAWING NO
	APPD -	4:1	202625
	PRODUCT SPEC -	SHEET 1 OF 1	
FINISH	APPLICATION SPEC -		
-	WEIGHT -		