






- 1 WIRE RANGE: .5–2mm² [20–14 AWG].
INSULATION RANGE: 3.30–5.08[.130–.200] DIA.
- 2 DIMENSIONS IN BRACKETS ARE IN INCHES.



SECTION B–B
SCALE 10:1



SECTION A–A
SCALE 10:1

		PRE-TIN		0.30[.012] BRASS		2029452-1	
		FINISH		MATERIAL		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN HOLAL 24JAN2013		TE TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK MICHIELUTTI, T 24JAN2013					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD MICHIELUTTI, T 24JAN2013		NAME SOCKET, UNIVERSAL MATE-N-LOK(TM) II —		
			PRODUCT SPEC				
			—				
			APPLICATION SPEC				
			—				
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE TABLE		SEE TABLE		A2	00779	C=2029452	—
CUSTOMER DRAWING				SCALE	4:1		SHEET
						1 of 1	REV
							A