




| LOC |  | DIST |  | REVISIONS |     |                       |         |     |      |
|-----|--|------|--|-----------|-----|-----------------------|---------|-----|------|
| —   |  | —    |  | P         | LTR | DESCRIPTION           | DATE    | DWN | APVD |
|     |  |      |  |           | R   | REV PER ECO-15-016062 | 09NOV15 | KG  | CD   |



1. THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308
2. MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .054 DIA
3. METAL RETENTION CLIPS ARE INCLUDED IN INSERTS
4. PACKAGE STAMPED M 24308/2-291F
5. THIS RCPT. WILL ACCEPT SIZE 22 SOCKET CONTACT M 39029/57-354 OR ANY AMP HDD-22 SOCKET CONTACT

- AMP PART NO. STAMPED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS
- UL/CSA DESIGNATION STAMPED IN THIS AREA,OPTIONAL

|                   |                |                                  |          |
|-------------------|----------------|----------------------------------|----------|
| SUPSD BY 204510-1 | STEEL, CLASS G | PHENOLIC<br>COLOR: BLACK         | 204510-3 |
| SUPSD BY 206065-4 | BRASS          | DIALLYL PATHALATE<br>COLOR: BLUE | 204510-2 |
|                   | STEEL, CLASS G | DIALLYL PATHALATE<br>COLOR: BLUE | 204510-1 |
|                   | SHELL MAT'L    | INSERT MAT'L                     |          |

|                                        |  |                                                              |                               |                                                    |  |
|----------------------------------------|--|--------------------------------------------------------------|-------------------------------|----------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>C.C.THOMAS<br>CHK<br>F.C.BALLEW III<br>APVD<br>D.J.M. | 12-2-87<br>1-25-88<br>1-26-88 | TE Connectivity                                    |  |
| DIMENSIONS:<br>INCHES                  |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:                       |                               | NAME                                               |  |
| 0 PLC ± -                              |  | 1 PLC ± -                                                    |                               | AMPLITE RCPT. FOR SOCKET CONTACTS                  |  |
| 2 PLC ± -                              |  | 3 PLC ± .005                                                 |                               | HI-DENSITY 'D' CONNECTOR                           |  |
| 4 PLC ± -                              |  | ANGLES ± -                                                   |                               | SIZE 6 (104 POSN) SERIES 90                        |  |
| MATERIAL<br>SEE TABLE                  |  | FINISH<br>SEE CALLOUTS                                       |                               | SIZE<br>CAGE CODE<br>DRAWING NO<br>A100779C=204510 |  |
| WEIGHT<br>-                            |  | RESTRICTED TO<br>-                                           |                               | SCALE<br>4:1                                       |  |
| CUSTOMER DRAWING                       |  | SHEET<br>1 of 1                                              |                               | REV<br>R                                           |  |