



D

C


B

A



FIBER CONNECTIVITY		
ODC SOCKET		
PIN 1	↔	LC CONNECTOR
PIN 2	↔	NOT CONNECTED

LABEL DETAIL: 3



NOTES:

- 1 REFER TO TE CONNECTIVITY CUSTOMER DRAWING 2064160 FOR CABLE ASSEMBLY LOSS AND WAVELENGTHS THAT CABLE ASSEMBLY LOSS WILL BE TESTED TO
- 2 STANDARD LENGTHS AND LENGTH TOLERANCE ACC. TO TE CONNECTIVITY CUSTOMER DRAWING 1985945
- 3 INFORMATION ON LABEL SEE DETAIL:
- BARCODE
 - UNIQUE SERIAL NUMBER
 - OPTIONAL FIELD
 - TE CONNECTIVITY PART NUMBER
 - TE CONNECTIVITY ORDER NUMBER
- * FOR L < 0.4 METER LABEL IS PLACED INSIDE OR WITH THE UNIT PACKAGE

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1985945	
PART NUMBER	"L" (meter) 2
X-2061422-Y	X.Y0
9-2061422-1	0.25 3
9-2061422-2	10.0

1	FOAC INFORMATION LABEL	4
1	LC CONNECTOR ASSEMBLY, MULTI MODE, BEIGE	3
1	FOKIT ODC SOCKET ASSEMBLY, MULTI MODE, VINYL CAP	2
L	FOCAB ODC 1.9 mm MULTI MODE 62/125, ORANGE	1
Qty	Description	Item
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: METERS		TOLERANCES UNLESS OTHERWISE SPECIFIED:
MATERIAL		FINISH
WEIGHT		CUSTOMER DRAWING
SCALE		SHEET
REV		A