


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
H	-	1	INITIAL PRELIMINARY ISSUE	12JUL2013	RC	EV



FIBER CONNECTIVITY		
ODVA	BUFFER	LC/DPX
1	BLUE	B
2	ORANGE	A

PART NUMBER	"L" (METER)		MAXIMUM Δ ATTENUATION (dB)
	MIN	MAX	
Δ 2061755-1	1.00	1.10	0.50
2061755-5	5.00	5.10	0.50

NOTES:

- Δ 1 MAXIMUM CONNECTOR INSERTION LOSS IS 0.5 dB PLUS CABLE ATTENUATION OF 0.7dB/km AT 1310 nm. (SEE TABLE)
- Δ 2 MINIMUM RETURN LOSS: 55 dB (1310 nm). NOT REQUIRED FOR ASSEMBLIES \leq 3 METERS
- 3 FILLED OUT TEST RESULT SHEET SUPPLIED WITH EACH INDIVIDUALLY PACKED ASSEMBLY
- Δ 4 INFORMATION ON LABEL SEE DETAIL:
 - BARCODE
 - UNIQUE TE SERIAL NUMBER
 - ASSEMBLY LENGTH
 - TE CONNECTIVITY PART NUMBER
 - TE CONNECTIVITY ORDER NUMBER
- 5 CABLE INFORMATION:
 - FIBER CORE DIAMETER: 9/125 μ m
 - OUTER JACKET DIAMETER: 7.5 mm
 - OUTER JACKET COLOUR: BLACK
 - OUTER JACKET MATERIAL: PVC

DESIGN APPROVED THIS PRINT IS
PRELIMINARY
 TO FIRST PIECE APPROVAL
 CONTACT PRODUCT ENGINEERING
 BEFORE USING THIS PRINT

LABEL DETAIL: Δ 4



Qty	Description	Item
2	FOAC INFORMATION LABEL	5
1	LC DUPLEX CONNECTOR ASSEMBLY, SINGLE MODE, BLUE	4
1	FOAC HEAT SHRINK TUBING, BLACK	3
1	PLUG SUBASSY, LC ODVA INDUSTRIAL CONNECTOR, WITH CAP	2
L	FOCAB 7.5 mm 2FOLD, SINGLE MODE 9/125, BLACK	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 05JUL2013																				
DIMENSIONS: mm		CHK A. HENGELMOLEN 12JUL2013																				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD E. VERVOORT 12JUL2013	NAME FIBER OPTIC LEAD 7.5 mm LC/DPX WITH ODVA ADAPTER - LC/DPX SINGLE MODE 9/125																			
<table border="1"> <tr><td>0 PLC</td><td>\pm</td><td>-</td></tr> <tr><td>1 PLC</td><td>\pm</td><td>-</td></tr> <tr><td>2 PLC</td><td>\pm</td><td>-</td></tr> <tr><td>3 PLC</td><td>\pm</td><td>-</td></tr> <tr><td>4 PLC</td><td>\pm</td><td>-</td></tr> <tr><td>ANGLES</td><td>\pm</td><td>-</td></tr> </table>		0 PLC	\pm	-	1 PLC	\pm	-	2 PLC	\pm	-	3 PLC	\pm	-	4 PLC	\pm	-	ANGLES	\pm	-	PRODUCT SPEC -	SIZE A2	CAGE CODE 00779
0 PLC	\pm	-																				
1 PLC	\pm	-																				
2 PLC	\pm	-																				
3 PLC	\pm	-																				
4 PLC	\pm	-																				
ANGLES	\pm	-																				
MATERIAL -		FINISH -	WEIGHT -	DRAWING NO C-2061755																		
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1																		
			REV 1																			

2061755