





ASSEMBLY CONNECTIVITY	
FULLAXS LC	BUFFER
PIN A	RED
PIN B	BLUE

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-2061940-Y	XY.0
9-2061940-9	100.0 -0/+3.0
9-2061940-8	150.0 -0/+3.0
9-2061940-7	200.0 -0/+3.0
9-2061940-6	250.0 -0/+3.0
9-2061940-5	300.0 -0/+3.0
9-2061940-4	350.0 -0/+3.0
9-2061940-3	400.0 -0/+3.0
9-2061940-2	450.0 -0/+3.0
9-2061940-1	500.0 -0/+3.0

- NOTES:
- 1 MAX. CONNECTOR ATTENUATION 0.3 dB, MEASURED AT 1310 nm AND 1550 nm ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
 - 2 MIN. RETURN LOSS 45 dB, IN MATED CONDITION AGAINST REFERENCE CONNECTOR AT 1310 nm AND 1550 nm
 - 3 INFORMATION ON LABEL, SEE DETAIL FOR EXAMPLE
 - BARCODE
 - UNIQUE TE SERIAL NUMBER
 - ASSEMBLY LENGTH
 - TE CONNECTIVITY PART NUMBER & ORDER NUMBER
 - 4 CABLE INFORMATION:
 - CORE DIAMETER: 9/125 µm (2x)
 - OUTER JACKET DIAMETER: 4.8 mm
 - OUTER JACKET COLOUR: BLACK
 - OUTER JACKET MATERIAL: HALOGEN FREE FLAME RETARDANT
 - CABLE ATTENUATION: 0.40 dB/km @ 1310 nm OR 0.25 dB/km @ 1550 nm

1	INFORMATION LABEL	4
1	FULLAXS OVERMOLDED LC DUPLEX PLUG ASSEMBLY, SM, BLACK	3
1	FULLAXS OVERMOLDED DROP PROTECTION, BLACK	2
L	FOCAB Ø4.8 mm, GLARO, 2FOLD, SINGLE MODE G657A2, BLACK	1
Qty	Description	Item
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:
MATERIAL		FINISH
DWN R. COOLEN 07JUL2014		CHK T. DRIJFHOUT 07JUL2014
APVD S. BORGAS 07JUL2014		NAME
PRODUCT SPEC		APPLICATION SPEC
114-32032		SIZE A2
WEIGHT		CAGE CODE 00779
CUSTOMER DRAWING		DRAWING NO C-2061940
SCALE NTS		SHEET 1 OF 1
		REV A

3 LABEL DETAIL:

