



8				7							
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				2016			
© COPYRIGHT 2016				BY -				ALL RIGHTS RESERVED.			
PART NUMBER		FIRST USED		MAXIMUM FEED STROKE		REBUILD KIT PART NUMBER 					
2063440-1		-		1.000		2217901-1				OBSOLETE	
2063440-2		-		1.500		2217901-2				OBSOLETE	
2063440-3		-		2.000		2217901-3				OBSOLETE	

OCEAN APPLICATOR



-  RECOMMENDED SPARE PARTS.
-  ASSEMBLE WITH LOCTITE 242, (NOT SUPPLIED BY TE CONNECTIVITY).
-  ASSEMBLE USING PARKERLUBE O-RING LUBRICANT, 884-4, (NOT SUPPLIED BY TE CONNECTIVITY).
-  LUBRICATE WITH ANDEROL 757 GREASE OR EQUIVALENT, (NOT SUPPLIED BY TE CONNECTIVITY).
-  SEAL REBUILD KIT PART NUMBER IS 2217901-4.

2	1	1	1	-	1803698-1	VALVE ASSEMBLY, CARTRIDGE	37
2	4	4	4	-	2079844-1	SPRING PLUNGER, M4	36
	1	1	1	-	2168039-2	PLUG, M5x0.8	35
	2	2	2	-	1-519012-9	SCR, SET, SOC, CONE POINT, M3 x 4.0	34
	1	1	1	-	2168083-2	SCR, SKT HD CAP, RoHS, M4 X 8.0	33
	2	2	2	-	9-18023-1	SCR, SKT HD CAP M5 X 60.0	32
	-	2	2	-	1-994236-7	SCR, FLT SKT HD CAP M4 X 8.0	31
	1	1	1	-	4-18024-4	SCR, BTN SKT HD CAP (M4 X 6.0)	30
	14	12	10	-	5-18024-7	SCR, BTN SKT HD CAP (M3 X 5.0)	29
	1	1	1	-	993083-4	CONNECTOR,ELBOW,90°,MINI	28
	600	600	600	mm	2030758-3	TUBING, 6MM POLYUERETHANE	27
3	2	2	2	-	2079160-3	SPRING PLUNGER, M4	26
	2	2	2	-	2168890-1	RING, RETAINING, INTERNAL	25
	1	1	1	-	2168889-1	RING, RETAINING, INTERNAL	24
3 1	2	2	2	-	6-21084-7	O-RING	23
3 1	3	3	3	-	5-21084-1	O-RING	22
	2	2	2	-	2079747-1	FLOW CONTROL	20
1	1	-	-	-	2217088-3	GASKET, AIR FEED	19
1	-	1	-	-	2217088-2	GASKET, AIR FEED	18
1	-	-	1	-	2217088-1	GASKET, AIR FEED	17
	1	-	-	-	2217277-1	COVER PLATE, AIR FEED, 2 INCH STROKE	16
	-	1	-	-	2217274-1	COVER PLATE, AIR FEED, 1.5 INCH STROKE	15
	-	-	1	-	2217075-1	COVER PLATE, AIR FEED, 1 INCH STROKE	14
	1	1	1	-	2161902-1	CAP, FEED ADJUST	13
	1	1	1	-	2217397-1	WHEEL, ADJUST	12
	1	1	1	-	2119454-1	KNOB, FEED ADJUST	11
	1	1	1	-	2161567-1	TAG, AIR SUPPLY LINE	10
	2	2	2	-	2161905-1	GUIDE, FEED ARM	9
	1	1	1	-	2217078-1	ARM, FEED	8
1	2	2	2	-	2217396-1	BUSHING, SHAFT SUPPORT	7
3 4	1	-	-	-	2161874-3	PISTON, AIR FEED	6
3 4	-	1	-	-	2161874-2	PISTON, AIR FEED	5
3 4	-	-	1	-	2161874-1	PISTON, AIR FEED	4
	1	-	-	-	2217264-1	HOUSING, AIR FEED, 2 INCH STROKE	3
	-	1	-	-	2217263-1	HOUSING, AIR FEED, 1.5 INCH STROKE	2
	-	-	1	-	2217087-1	HOUSING, AIR FEED, 1 INCH STROKE	1
	-3	-2	-1	U/M	PART NO	DESCRIPTION	ITEM NO

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN GOPALAKRISHNA HV 06MAY2016		 TE Connectivity	
				CHK TIMOTHY ELBIN 06MAY2016			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD TIMOTHY ELBIN 06MAY2016		NAME	
MM				PRODUCT SPEC		AIR FEED MODULE	
		0 PLC ±		APPLICATION SPEC		-	
		1 PLC ±				-	
		2 PLC ±					
		3 PLC ±					
		4 PLC ±					
MATERIAL		FINISH		WEIGHT		SIZE	
-		-		-		A1	
-		-		-		CAGE CODE	
-		-		-		DRAWING NO	
-		-		-		C=2063440	
-		-		-		RESTRICTED TO	
-		-		-		-	
CUSTOMER DRAWING				SCALE		1:1	
				SHEET		1 OF 1	
				REV		C2	