







SECTION W - W

- △ MATERIAL:
CONTACT - PHOS BRONZE
HOUSING - LCP, UL 94V-0, COLOR - BLACK
- △ FINISH: CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-2303-1; BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III, APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE). COMPLIANT PIN AREA - 0.5um MATTE TIN OVER 1.27um MIN NICKEL
- △ 3 CONNECTOR MARKED WITH PART NUMBER, DATE CODE, 85 OHM, AND STANDARD IN APPROXIMATE AREA SHOWN
- △ 4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
5. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- △ 6 REFERENCE APPLICATION SPEC FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- △ 7 SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIMATE AREA.



○ = SIGNAL
 ⊗ = GROUND

RECOMMENDED PC BOARD
 LAYOUT BACKPLANE,
 COMPONENT SIDE SHOWN
 SCALE 6:1

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	J.K.SHOBER	09DEC2009		
				CHK	C.RITTER	09DEC2009		
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:				NAME	TE Connectivity	
mm								
		0 PLOC ± 1 PLOC ± 2 PLOC ± 4 PLOC ± ANGLES ± FINISH						
MATERIAL						PRODUCT SPEC	HEADER ASSEMBLY, LEFT WALL	
						108-2303-1	5 PAIR, 8 COLUMN	
						APPLICATION SPEC	TinMon 85 OHM	
						114-13243		
						WEIGHT		
							SIZE	CASE CODE
							DRAWING NO	
							RESTRICTED TO	
						A1	00779	C-2065738
CUSTOMER DRAWING						SCALE	6:1	SHEET
							1	OF
								REV C