





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	T	REVISED PER ECR-24-213594	01JUL2024	RK	FJS



- 1 HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3 3.81µm [.000150] MIN TIN-LEAD OVER 1.27µm [.000050] MIN NICKEL.
- 4 0.76µm [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81µm [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 5 3.81µm [.000150] MIN TIN OVER 1.27µm [.000050] MIN NICKEL.
- 6 0.76µm [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81µm [.000150] MIN TIN FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 7 PRELIMINARY PART NUMBER.

OBSOLETE	3.50[.137]	6	YES	1-207530-1
OBSOLETE		6	NO	1-207530-0
		6	YES	207530-9
		5	NO	207530-8
		5	YES	207530-7
OBSOLETE	4.60[.181]	4	NO	207530-4
OBSOLETE		4	YES	207530-3
OBSOLETE		3	NO	207530-2
OBSOLETE		3	YES	207530-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03/19/92		 TE Connectivity	
		L.SIPE			
		CHK 3-25-92		NAME	
		R.STONE			
		APVD 3-25-92		SOCKET HEADER ASSEMBLY, 18 POSITION, METRIMATE	
		A.TRAVIS			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-10033	
		APPLICATION SPEC —		SIZE	
				CAGE CODE	
MATERIAL		FINISH		DRAWING NO	
				RESTRICTED TO	
SEE NOTE		CONTACT: SEE TABLE		WEIGHT —	
				A2 00779 C=207530	
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 1
				REV T	