


1	RECEPTACLE IS LOADED WITH 4 TYPE III+ POSTED PIN CONTACTS.
2	CONTACT BODY: GOLD PER MIL-G-45204 OVER NICKEL PER QQ-N-290. CONTACT POST: TIN-LEAD PER MIL-T-10727 OVER COPPER PER MIL-C-14550A.
3	CONTACT BODY: PRECIOUS METAL PLATE OVER NICKEL PER QQ-N-290. CONTACT POST: TIN OVER COPPER PER MIL-C-14550A.
4	CONTACT BODY: TIN OVER NICKEL PER MIL-C-14550A CONTACT POST: TIN OVER NICKEL PER MIL-C-14550A



		.220	YES	NO	1-207825-5
OBSOLETE		.429	YES	YES	1-207825-4
OBSOLETE		.119	NO	NO	1-207825-2
		.618	NO	YES	1-207825-1
OBSOLETE		.119	YES	YES	1-207825-0
		.119	NO	YES	207825-9
OBSOLETE		.220	YES	NO	207825-8
OBSOLETE		.429	YES	YES	207825-7
OBSOLETE		.119	NO	NO	207825-6
OBSOLETE		.119	NO	NO	207825-5
OBSOLETE		.618	NO	YES	207825-4
OBSOLETE		.119	YES	YES	207825-3
OBSOLETE		.220	NO	YES	207825-2
OBSOLETE		.119	NO	YES	207825-1

CONTACT FINISH	A	PERIPHERAL SEAL	THREADED INSERTS	PART NUMBER
-------------------	---	--------------------	---------------------	----------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.LEE BG 7-1-91		 TE Connectivity				
		CHK W.G.LENKER 4-14-92						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± ± -		NAME RECEPTACLE ASSEMBLY, POSTED, STD SEX, SERIES 1, 11-4, CPC -				
		PRODUCT SPEC 108-10024						
		APPLICATION SPEC -						
		WEIGHT -						
MATERIAL -		FINISH -		SIZE A2	CAGE CODE 00779	DRAWING NO C-207825	RESTRICTED TO -	
CONTACT:  2		CUSTOMER DRAWING				SCALE 2:1	SHEET 1 of 1	REV 11

RECOMMENDED P.C. BOARD LAYOUT