






	#4-40 THREADED INSERTS	NO	YES	.557		ALL	3-208224-0
OBSOLETE	Ø.125 HOLES	NO	NO	.547		ALL	2-208224-9
		NO	NO	.490		ALL	2-208224-8
YES		YES	.368		1-17, 19-37	2-208224-5	
NO		NO	.557		1-9, 11-31, 33-37	2-208224-4	
OBSOLETE	#4-40 THREADED INSERTS	NO	YES	.557		ALL	2-208224-3
OBSOLETE	Ø.125 HOLES	NO	NO	.368		ALL	2-208224-2
		NO	NO	.557		ALL	2-208224-1
		NO	YES	.368		1-10, 12-29, 31-37	1-208224-8
		NO	YES	.368		4,8,10,23,31,34-36	1-208224-7
		NO	YES	.368		1-10, 12-29, 31-37	1-208224-6
		NO	YES	.368		1-22, 24-37	1-208224-5
OBSOLETE		NO	NO	.368		ALL	1-208224-3
		NO	YES	.368		1-10, 12-29, 31-37	1-208224-2
		NO	YES	.368		1-22, 24-37	1-208224-1
OBSOLETE		NO	YES	.368		1-10, 12-29, 31-37	1-208224-0
OBSOLETE		NO	NO	.368		ALL	208224-9
OBSOLETE		NO	YES	.368		1-22, 24-37	208224-5
OBSOLETE		NO	YES	.368		4,8,10,23,31,34-36	208224-4
		NO	YES	.368		1-10, 12-29, 31-37	208224-3
		NO	NO	.368		ALL	208224-2
OBSOLETE		NO	NO	.557		ALL	208224-1
	MOUNTING FEATURES	FLANGE SEAL	PERIPHERAL SEAL	L	CONTACT FINISH	SELECT LOADED IN POSITIONS	PART NUMBER

RECOMMENDED PC BOARD LAYOUT

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

- 1 HOUSING: THERMOPLASTIC, COLOR: BLACK.
- 2 PERIPHERAL SEAL: ELASTOMER, COLOR: BLACK.
- 3 CONTACT:
BODY - BRASS, .000030 MIN PRECIOUS METAL PLATE FOR A LENGTH OF .200 MIN FROM MATING END, GOLD FLASH ON REMAINDER, BOTH OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL.
- 4 CONTACT:
BODY - BRASS, .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL.
- 5 CONTACT:
BODY - BRASS, .000100 MIN TIN OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN OVER .000050 MIN NICKEL.
- 6 .009 MAXIMUM CONTACT LEAD-IN SEAM GAP PERMISSIBLE ON MATING FACE END.
- 7 CONTACT:
BODY - BRASS, .000030 MIN PRECIOUS METAL PLATE FOR A LENGTH OF .200 MIN FROM MATING END, GOLD FLASH ON REMAINDER, BOTH OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN.
- 8 FLANGE SEAL: ELASTOMER, COLOR: BLACK.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S.WELDON

26FEB2003

CHK
S.HEADER

26FEB2003

APVD
S.HEADER

26FEB2003

TE Connectivity

NAME
RECEPTACLE ASSEMBLY, POSTED,
REVERSE SEX, SERIES 1, 23-37, CPC

DIMENSIONS:
INCHES

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±0.0
±0.00
±0.000
±0.0000
±

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

±
±0.0
±0.00
±0.000
±0.0000
±

PRODUCT SPEC
-
APPLICATION SPEC
-

SIZE
A

CAGE CODE
00779

DRAWING NO
208224

RESTRICTED TO
-

MATERIAL
-
-

WEIGHT
-

CUSTOMER DRAWING

SCALE
3:1

SHEET
2

OF
2

REV
AJ

4805 (3/13)