

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20




© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION

ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	ECO-17-010940	27JUL2017	YS	AG
	C2	ECO-18-002947	28FEB2018	YS	AG
	D	ECN-22-181755	23NOV2022	SS	PK



1. NO DAMAGES, SINK MARKS, CAVITIES OR FLOW LINES PERMITTED

2 MATERIAL:PA66 35% GLASS FILL
INHERENTLY LUBRICATED SILICONE

3 AROUND NO FLASH PERMITTED



C	2.70	LT. BLUE	40	SIZE A	I-2103731-1
D	2.85	TAN	30	SIZE B	I-2103731-2
D	4.00	GREEN	30	SIZE C	2103731-3
REV	DIM F	COLOR	DUROMETER	CABLE DIA	PART NO


THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 11APR2014
VISHWA. A
CHK 06MAY2014
D. SIMPSON
APVD 06MAY2014
A. TYLER

TE TE Connectivity

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:



0 PLC ±
1 PLC ±0.2
2 PLC ±0.10
3 PLC ±
4 PLC ±
ANGLES ±1°

MATERIAL



FINISH
-
-

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

NAME
SPACER-SEAL ASSY, OVERMOLDED,
PLUG, HVA280-2PI SE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	C-2103731	-

CUSTOMER DRAWING SCALE 2:1 SHEET 1 OF 1 REV D