

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , -

LOC

DIST

REVISIONS

© COPYRIGHT BY - Taipei, Taiwan

ALL RIGHTS RESERVED.

HY

-

P

LTR

DESCRIPTION

DATE

DWN

APVD


B

ECR-16-017100

02DEC2016

CL

VW



CONN.1	PIN ASSIGNMENT	CONN.2
1	RED	1
2	WHITE	2
3	GREEN	3
4	BLACK	5
5	BLUE	6
6	YELLOW	7
7	DRAIN WIRE	8
8	PURPLE	9
9	ORANGE	10
SHELL	BRAID	SHELL

TEST ALL PRODUCTS AS BELOW:
 100% OPEN & SHORT TEST.
 CONTACT RESISTANCE:3 OHM MAX.
 INSULATION RESISTANCE:10 MOHM MIN.
 WITHSTADING VOLTAGE 300V(DC) 0.1sec.

2117155-4	457±20
1-2117155-0	1000±20
PART NUMBER	L

QTY	U/M	DESCRIPTION	ITEM
1	PC	USB 3.0 PLUG, MICRO B TYPE, AU PLATED 30u" FOR CONTACT AREA	5
AR	MR	COPPER FOIL TAPE	4
AR	KG	OVER MOLDED PVC, COLOR: BLACK	3
1	PC	USB 3.0 PLUG, A TYPE, AU PLATED 30u" FOR CONTACT AREA	2
AR	MR	USB 3.0 CABLE, OD=4.5 (1P*32#+D+AL+Mylar)*2C+1P*32#+2C*26#+AL+B /UL20276	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WU 12,AUG,2011	TE Connectivity USB 3.0 A to Micro B Cable Ass'y	
DIMENSIONS: MM		CHK CP. ONG 12,AUG,2011		
		APVD W. WANG 12,AUG,2011	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± 3'		PRODUCT SPEC		
MATERIAL SEE NOTE		QUALIFICATION TEST REPORT		
FINISH SEE NOTE		SIZE A3	CAGE CODE 00779	DRAWING NO C=2117155
		WEIGHT		RESTRICTED TO -
		CUSTOMER DRAWING		SCALE - SHEET 1 of 2 REV B

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-, -

LOC

DIST

REVISIONS

© COPYRIGHT - BY - Taipei, Taiwan

ALL RIGHTS RESERVED.

HY

-

P

LTR

DESCRIPTION

DATE


DWN

APVD

SEE SHEET 1

-

-



PIN ASSIGNMENT		
CONN.1	COLOR	CONN.2
1	RED	1
2	WHITE	2
3	GREEN	3
4	BLACK	5
5	BLUE	6
6	YELLOW	7
7	DRAIN WIRE	8
8	PURPLE	9
9	ORANGE	10
SHELL	BRAID	SHELL

TEST ALL PRODUCTS AS BELOW:
 100% OPEN & SHORT TEST.
 CONTACT RESISTANCE:3 OHM MAX.
 INSULATION RESISTANCE:10 MOHM MIN.
 WITHSTADING VOLTAGE 300V(DC) 0.1sec.

2-2117155-0	2000±20
1-2117155-5	1500±20
PART NUMBER	L

QTY	U/M	DESCRIPTION	ITEM
1	PC	USB 3.0 PLUG, MICRO B TYPE, AU PLATED 30u" FOR CONTACT AREA	5
AR	MR	COPPER FOIL TAPE	4
AR	KG	OVER MOLDED PVC, COLOR: BLACK	3
1	PC	USB 3.0 PLUG, A TYPE, AU PLATED 30u" FOR CONTACT AREA	2
AR	MR	USB 3.0 CABLE, OD=5.5 (1P*28#+D+AL+Mylar)*2C+1P*28#+2C*24#+AL+B /UL20276	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WU 12,AUG,2011		
DIMENSIONS: MM		CHK CP. ONG 12,AUG,2011		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± 3'		APVD W. WANG 12,AUG,2011	NAME	
MATERIAL SEE NOTE		FINISH SEE NOTE	PRODUCT SPEC	
QUALIFICATION TEST REPORT		WEIGHT		RESTRICTED TO
CUSTOMER DRAWING		SIZE A3	CAGE CODE 00779	DRAWING NO C=2117155
SCALE -		SHEET 2 of 2		REV B