


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
E3		Updated cable length of -4	19APR2021	SJ CY
E4		REVISED	14JUN2022	SJ CY
E5		PRE_ADD 2118059-5	22NOV2022	SJ VK
E6		REVISED PER ECN-24-246522	08JAN2024	SJ JH



- NOTES: UNLESS OTHERWISE SPECIFIED.
1. SILKSCREEN TE LOGO, TE PN, REVISION LETTER ON TOP LAYER. FOLLOWED BY 4 DIGIT DATE CODE.
 2. MATERIAL: FR4, COPPER THICKNESS 1 OZ, CABLE- MHF or MHF4 WITH TE APPROVED EQUIVALENT. TOTAL THICKNESS 0.304 WITH OUT ADHESIVE.
 3. FINISH: ENIG-ELECTROLESS NICKEL IMMERSION GOLD ON EXPOSED SOLDER AREAS PRIOR TO SOLDERING.
 4. PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE CONNECTIVITY ENVIROMENTAL SPECIFICATION TEC-138-702.
 5. ADHESIVE; REMOVE PAPER BACKING OF PRESSURE SENSITIVE ADHESIVE TO APPLY.
 6. REFERENCE TE DATASHEET DS2118059-1 FOR ANTENNA SPECIFICS.

STE
 2118059 Rev D
 XXXX XXXXX

CONNECTOR MATING FACE DOWN IN THIS VIEW "C"

MHF	1.37	730.00	763.80	2118059-6
MHF 4L	1.13	400.00	433.80	2118059-4
MHF	1.37	116.20	150.00	2118059-3
MHF	1.37	316.20	350.00	2118059-1
"C" CONNECTOR TYPE	CABLE OD	B	A	PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SCHOLZ 22 JUL 2016	STE TE Connectivity	
		CHK J. SCHOLZ 22 JUL 2016		
DIMENSIONS: mm		APVD J. MOORE 22 JUL 2016	NAME WMAX SINGLE BAND, U.FL CABLE 2300 Mhz-3800<Mhz	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC -	APPLICATION SPEC -	
0 PLC ±		WEIGHT -	SIZE A2	CAGE CODE -
1 PLC ±		CUSTOMER DRAWING	DRAWING NO C-2118059	RESTRICTED TO -
2 PLC ±0.2		SCALE 4:1	SHEET 1 OF 1	REV E6
3 PLC ±				
4 PLC ±				
ANGLES ±				
FINISH -				