


| LOC | DIST | REVISIONS |     |                           |           |     |      |
|-----|------|-----------|-----|---------------------------|-----------|-----|------|
| 00  | AJ   | P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|     |      |           | A4  | Added cable parts.        | 13AUG2020 | SJ  | JH   |
|     |      |           | B   | REVISED PER ECO-20-015624 | 04NOV2020 | SJ  | JH   |
|     |      |           | B1  | REVISED PER ECN-25-321753 | 13MAY2025 | DW  | VK   |
|     |      |           | C   | REVISED PER ECN-25-328003 | 19JUN2025 | DW  | VK   |



7. SILKSCREEN; WHITE EPOXY INK

- A. TE LOGO, TE P/N
- B. WORD REV., FOLLOWED BY THE LATEST REVISION LETTER, AS SHOWN.
- C. 4 DIGIT DATE CODE: FIRST 2 DIGITS FOR THE WEEK CODE AND THE 2ND TWO DIGITS FOR THE YEAR CODE.  
OTHERS: SPECIFIC TE SOURCE CODE NUMBER DIGITS AS REQUIRED.

|                         |                       |          |        |                |
|-------------------------|-----------------------|----------|--------|----------------|
| UMCC GEN. 4<br>(MHF 4L) | BLACK                 | (204.20) | 200.00 | 1-2118909-8    |
|                         | BLACK                 | (154.20) | 150.00 | 1-2118909-7    |
|                         | BLACK                 | (104.20) | 100.0  | 1-2118909-6    |
|                         | BLACK                 | (54.20)  | 50.0   | 1-2118909-5    |
|                         | BLACK                 | (375.00) | 370.80 | 2118909-6      |
|                         | BLACK                 | (225.00) | 220.80 | 2118909-5      |
|                         | BLACK                 | (120.00) | 115.80 | 2118909-4      |
| UMCC GEN. 1<br>(MHF 1)  | WHITE                 | (554.20) | 550.00 | 2-2118909-5    |
|                         | BLUE                  | (454.20) | 450.00 | 2-2118909-4    |
|                         | BLACK                 | (204.20) | 200.00 | 1-2118909-4    |
|                         | BLACK                 | (154.20) | 150.00 | 1-2118909-3    |
|                         | BLACK                 | (104.20) | 100.00 | 1-2118909-2    |
|                         | BLACK                 | (54.20)  | 50.00  | 1-2118909-1    |
|                         | BLACK                 | (64.20)  | 60.00  | 2118909-8      |
|                         | BLACK                 | (273.00) | 268.80 | 2118909-2      |
|                         | BLACK                 | (120.00) | 115.80 | 2118909-1      |
| "C" CONNECTOR<br>TYPE   | CABLE JACKET<br>COLOR | B        | A      | PART<br>NUMBER |

|                                                                                       |  |                                                                                                                                    |  |                                                                                                       |        |
|---------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN 04APR2020<br>CHK SJ.NOH<br>H.SHIN<br>APVD JH.KIM<br>04APR2020                                                                  |  |  TE Connectivity |        |
| DIMENSIONS:<br>mm                                                                     |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ±.<br>1 PLC ±.<br>2 PLC ±.<br>3 PLC ±.<br>4 PLC ±.<br>ANGLES ±.<br>MATERIAL FINISH |  | NAME<br>PCB Ant, MHF/MHF4L<br>Wi-Fi 6E Triple                                                         |        |
|  |  | PRODUCT SPEC<br>-<br>APPLICATION SPEC<br>-<br>WEIGHT -                                                                             |  | SIZE<br>A2                                                                                            |        |
| MATERIAL<br>-                                                                         |  | WEIGHT<br>-                                                                                                                        |  | CAGE CODE<br>00779                                                                                    |        |
| MATERIAL<br>-                                                                         |  | WEIGHT<br>-                                                                                                                        |  | DRAWING NO<br>C-2118909                                                                               |        |
| MATERIAL<br>-                                                                         |  | WEIGHT<br>-                                                                                                                        |  | RESTRICTED TO<br>-                                                                                    |        |
| CUSTOMER DRAWING                                                                      |  |                                                                                                                                    |  | SCALE                                                                                                 | 4:1    |
|                                                                                       |  |                                                                                                                                    |  | SHEET                                                                                                 | 1 OF 1 |
|                                                                                       |  |                                                                                                                                    |  | REV                                                                                                   | C      |