




REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
C		REVISED PER ECR-20-017946	24SEP2021	AP EC




- 1 CABLE ASSEMBLY TESTED FOR OPENS, SHORTS AND HI-POT @ 300V.
- 2 LABEL INFORMATION:
 

	2127833-	TE LOGO & TE CONNECTIVITY PART NUMBER
MINI-SAS	6Gbps	
---	METERS	LENGTH
YYWW		DATE CODE
MADE IN	---	COUNTRY OF ORIGIN


- 3. PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE CONNECTIVITY STANDARD TEC-138-702.
- 4. PRODUCT MEETS THE REQUIREMENTS OF T10/2125-D, REVISION 04b [SAS-2.1].

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN T.SMITH 24FEB2010	TE Connectivity Ltd.
DIMENSIONS: mm		CHK J.HACKMAN 24FEB2010	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.HACKMAN 24FEB2010	NAME
0 PLC ± -			CABLE ASSEMBLY, MINI-SAS, 4X, EXTERNAL
1 PLC ± -			6 Gbps, PASSIVE
2 PLC ± -			APPLICATION SPEC
3 PLC ± -			SIZE
4 PLC ± -			CAGE CODE
ANGLES ± -			DRAWING NO
			RESTRICTED TO
MATERIAL	FINISH	WEIGHT	A1 00779 C=2127833
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 2 REV C


REVISIONS				
P	LTR	DESCRIPTION	DATE	APPD
-		SEE SHEET 1	-	-




KEY SLOT 2-4




KEY SLOT 2-4, KEY RIB 3




KEY SLOT 4-6



KEY SLOT 4-6, KEY RIB 3



KEY SLOT 2-4-6



KEY SLOT 2-4-6, KEY RIB 3

3	3	2-4-6	2-4-6	6 GBPS	24 AWG	10±0.15 METERS	2-2127833-6
3	3	2-4-6	2-4-6	6 GBPS	24 AWG	9±0.15 METERS	2-2127833-5
3	3	2-4-6	2-4-6	6 GBPS	24 AWG	8±0.125 METERS	2-2127833-4
3	3	2-4-6	2-4-6	6 GBPS	24 AWG	7±0.1 METERS	2-2127833-3
-	-	2-4-6	2-4-6	6 GBPS	24 AWG	6±0.075 METERS	2-2127833-2
-	-	2-4-6	2-4-6	6 GBPS	24 AWG	5±0.075 METERS	2-2127833-1
-	-	2-4-6	2-4-6	6 GBPS	26 AWG	4±0.075 METERS	2-2127833-0
-	-	2-4-6	2-4-6	6 GBPS	26 AWG	3±0.05 METERS	1-2127833-9
-	-	2-4-6	2-4-6	6 GBPS	28 AWG	2.5±0.05 METERS	1-2127833-8
-	-	2-4-6	2-4-6	6 GBPS	28 AWG	2±0.05 METERS	1-2127833-7
-	-	2-4-6	2-4-6	6 GBPS	28 AWG	1.5±0.04 METERS	1-2127833-6
OBSOLETE	-	2-4-6	2-4-6	6 GBPS	30 AWG	1±0.04 METERS	1-2127833-5
OBSOLETE	-	2-4-6	2-4-6	6 GBPS	30 AWG	0.5±0.025 METERS	1-2127833-4
3	3	2-4	4-6	6 GBPS	24 AWG	10±0.15 METERS	1-2127833-3
3	3	2-4	4-6	6 GBPS	24 AWG	9±0.15 METERS	1-2127833-2
3	3	2-4	4-6	6 GBPS	24 AWG	8±0.125 METERS	1-2127833-1
3	3	2-4	4-6	6 GBPS	24 AWG	7±0.1 METERS	1-2127833-0
-	-	2-4	4-6	6 GBPS	24 AWG	6±0.075 METERS	2127833-9
-	-	2-4	4-6	6 GBPS	24 AWG	5±0.075 METERS	2127833-8
-	-	2-4	4-6	6 GBPS	26 AWG	4±0.075 METERS	2127833-7
-	-	2-4	4-6	6 GBPS	26 AWG	3±0.05 METERS	2127833-6
-	-	2-4	4-6	6 GBPS	28 AWG	2.5±0.05 METERS	2127833-5
-	-	2-4	4-6	6 GBPS	28 AWG	2±0.05 METERS	2127833-4
-	-	2-4	4-6	6 GBPS	28 AWG	1.5±0.04 METERS	2127833-3
OBSOLETE	-	2-4	4-6	6 GBPS	30 AWG	1±0.04 METERS	2127833-2
-	-	2-4	4-6	6 GBPS	30 AWG	0.5±0.025 METERS	2127833-1
P1	P2	P1	P2	DATA RATE	WIRE GAGE	L	PART NO
KEY RIB		KEY SLOTS					

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN T.SMITH 24FEB2010	TE Connectivity Ltd.
0. PLC ± - 1. PLC ± - 2. PLC ± - 3. PLC ± - 4. PLC ± - ANGLES ± -		CHK J.HACKMAN 24FEB2010 APPD J.HACKMAN 24FEB2010 PRODUCT SPEC	
MATERIAL	FINISH	NAME CABLE ASSEMBLY, MINI-SAS, 4X, EXTERNAL 6 Gbps, PASSIVE	
		APPLICATION SPEC SIZE A1 CAGE CODE 00779 DRAWING NO. 2127833 WEIGHT CUSTOMER DRAWING	RESTRICTED TO SCALE 1:1 SHEET 2 OF 2 REV C