

RECOMMAND P.C.B LAYOUT
SCALE 4:1

1. BE USE ALTOGETHER THE HEADER AND TYCO ELECTRONICS'S FRAME
2. SOLDER PAD

COPPER ALLOY
Au 0.0002mm MIN., TIN 0.002mm MIN.
Ni 0.00127mm MIN. UNDERPLATING ALL OVER

	HIGH TEMP THERMOPLASTIC
	UL94 V-0
R	COLOR:BLACK

26

2129256-1

② CONTACT

① HEADER HSG

POS.

PART NUMBER —

MATERIAL & FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	12JAN11
-----	---------

CHK	12JAN11
W. CHEN	

W.CHEN	
APVD	12JAN11
M. CHAO	

M. CHAO
PRODUCT SPEC

108-99000

APPLICATION	SPEC
501	88000

501-99000	
WEIGHT	

CUSTOMER DRAWING

CUSTOMER DRAWING



**Tyco
Electronics**

Tyco Electronics Corporation
Taipei, Taiwan

1	NAME
---	------

HEADER ASSEMBLY

TOP MOUNT, CARD PUSH,
EXPRESSCARD CONNECTOR

SIZE

CAGE CODE

DRAWING NO

©-2129288

~~RESTRICTED TO~~

SCALE 1:1

SHEET 1 OF 2

REV	Λ
-----	---

3306-7 (1/08)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

©

COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR


DESCRIPTION

DATE





DWN

APVD

SEE SHEET 1





PULL OUT DIRECTION




3. PACKING MATERIAL: CARRIER TAPE: HIPS; COLOR: CLEAR.
COVER TAPE: PET; COLOR: CLEAR.
4. CARTON DIMENSIONS: 355X355X310

250	4	1000
PCS/REEL	REEL/CARTON	TOTAL Q'TY

DETAIL G
SCALE 10:1DETAIL F
SCALE: FREE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±	±0.5
1 PLC	±	±2
2 PLC	±	±
3 PLC	±	±
4 PLC	±	±
ANGLES	±	±
FINISH	±	±

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco
ElectronicsTyco Electronics Corporation
Taipei, Taiwan

NAME

HEADER ASSEMBLY
TOP MOUNT, CARD PUSH,
EXPRESSCARD CONNECTOR

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

2129288

SCALE

NON

SHEET

2 OF 2

REV

A