




4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

©

COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN


APVD

- SEE SHEET 1


-

-

-



REFERENCE P.C.BOARD LAYOUT
VIEW FROM COMPONENT MOUNTING SIDE
(TOLERANCES : ±0.1)




REFERENCE P.C.BOARD LAYOUT
(SCALE 4:1)
(HEADER CONNECTOR MOUNTING LAYOUT DETAIL)
TOLERANCE ±0.05

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 RLC ±
1 PLC ± ±0.5
2 PLC ± ±2°
3 PLC ±
4 PLC ±
ANGLES ±
FINISH ±

MATERIAL

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

EJECTOR ASSEMBLY
TOP MOUNT, CARD PUSH TYPE
EXPRESS CARD CONNECTOR

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2129346

SCALE

2:1

SHEET

2 OF 4

REV

B

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

-

-

-

D

D

C


C

B


B

A


A



- ① GROUNDING PAD
- ② SOLDERING PAD
- ③ STAND OFF 1mm
- ④ NO COMPONENT AND NO SIGNAL LINE AREA
- ⑤ RECOMMENDED TIGHTENING TORQUE 0.10Nm MAX
- ⑥ BE USED IN CARD PUSH APPLICATION
- ⑦ ONLY DEFINE IN CARD PUSH TYPE EJECTOR.
- ⑧ HEADER ASS'Y. P/N: 2129347-1, APPLICABLE TO CARD PUSH TYPE PURCHASED SEPARATELY
- ⑨ ALLOWED MAXIMUM SCREW HEAD HEIGHT : 0.7mm MAX
- 10. THE STAMPING DIRECTION OF SHELL IS OUTWARD



E-E
SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CHK APVD		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES ± ± ± ± ± ± ±0.5 ±2° ±		NAME EJECTOR ASSEMBLY TOP MOUNT, CARD PUSH TYPE EXPRESS CARD CONNECTOR	
MATERIAL		FINISH		PRODUCT SPEC APPLICATION SPEC WEIGHT	
CUSTOMER DRAWING		SCALE 1:1		SHEET 3 OF 4	
				REV B	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.



COPYRIGHT - By -

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN


APVD

SEE SHEET 1


-

-



-

EXPRESS CARD
SHIELD FRAME ASSY


12




AIR CAP



BOX



TAPE

PACKAGE
BELT

12. MATERIAL:

TRAY: PET, COLOR: WHITE, t=0.8mm

13. BOX DIMENSION: 394mmX320mmX148mm

16

10

160

PCS/TRAY

TRAY/BOX

TOTAL Q'TY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC


APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

±

±

±

±

±

±

±

±0.5

±

±

±

±

±

±

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

EJECTOR ASSEMBLY
TOP MOUNT, CARD PUSH TYPE
EXPRESS CARD CONNECTOR

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2129346

SCALE

NON

SHEET

4 of 4

REV

B