






LOC DW	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—


2129516-1/-2; AS SHOWN

DC POWER JACK CONNECTOR
TE P/N: 2129516-1/-2



1. EU ROHS-RELATED RESTRICTED SUBSTANCE SPEC IN HOMOGENEOUS MATERIAL REFER TO TEC-138-702 REV.G:
LEAD < 1000PPM, CADMIUM < 100PPM, MERCURY < 1000PPM
CHROMIUM VI < 1000PPM, PBB <1000PPM, PBDE < 1000PPM
2. HALOGEN FREE SPEC:
CHLORINE (Cl): 900 ppm MAX.
BROMINE (Br): 900 ppm MAX.
CHLORINE (Cl) + BROMINE (Br): 1500 ppm MAX.
3. SHIPPING BOX DIMENSION: 445mmX445mmX270mm

144	25	3600
PCS/TRAY	TRAY/SHIPPING BOX	TOTAL Q'TY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	—	 TE Connectivity		
DIMENSIONS: mm		CHK	—	NAME DC POWER JACK CONNECTOR CABLE TYPE		
		APVD	—	SIZE A3		
		PRODUCT SPEC	—	CAGE CODE 00779		
MATERIAL		APPLICATION SPEC	—	DRAWING NO C-2129516		
		WEIGHT	—	RESTRICTED TO —		
		CUSTOMER DRAWING		SCALE	NA	SHEET
						2 OF 2
						REV
						A1