




-
- PIN A1
- KEEP-OUT ZONE
- 24.70
- 8.50
- 1.90 TYP
- 0.95
- 2.95
- 13.21
- 28.9
- 22.95
- 1.35 TYP
- 4.75
- SIGNAL HOLES REF
- GROUND HOLE REF
- ROW A
- ROW B
- ROW C
- ROW D
- ROW E
- ROW F
- ROW G
- ROW H
- ROW J
- ROW K
- ROW L
- ROW M
- ROW N
- ROW O
- ROW P
- ROW R
- ROW S
- ROW T
- $\varnothing 3.56 \pm 0.08$
- $\varnothing 0.15$
- UNPLATED SCREW HOLE
- $25 \times \varnothing 0.46 \pm 0.05$
- $\varnothing 0.10$
- PLATED THRU HOLE

28.6

20.4


$M \pm 0.20$

1.00
MINIMUM BOARD
THICKNESS

SECTION A-A

(2.64)

UNPLA
SCREW H



LOC		DIST		REVISIONS				
P	LYR	DESCRIPTION			DATE	OWN	APVD	
		SEE SHEET 1			-	-	-	

	H	5.5	8-2132000-6	OBSOLETE
	H	4.9	8-2132000-5	
	H	4.5	8-2132000-4	
	H	5.5	8-2132000-3	
	H	4.9	8-2132000-2	
	H	4.5	8-2132000-1	
	G	5.5	7-2132000-6	
	G	4.9	7-2132000-5	
	G	4.5	7-2132000-4	
	G	5.5	7-2132000-3	
	G	4.9	7-2132000-2	
	G	4.5	7-2132000-1	
	F	5.5	6-2132000-6	
	F	4.9	6-2132000-5	
	F	4.5	6-2132000-4	
	F	5.5	6-2132000-3	
	F	4.9	6-2132000-2	
	F	4.5	6-2132000-1	
	E	5.5	5-2132000-6	
	E	4.9	5-2132000-5	
	E	4.5	5-2132000-4	
	E	5.5	5-2132000-3	
	E	4.9	5-2132000-2	
	E	4.5	5-2132000-1	
	D	5.5	4-2132000-6	
	D	4.9	4-2132000-5	
	D	4.5	4-2132000-4	
	D	5.5	4-2132000-3	
	D	4.9	4-2132000-2	
	D	4.5	4-2132000-1	
	C	5.5	3-2132000-6	
	C	4.9	3-2132000-5	
	C	4.5	3-2132000-4	
	C	5.5	3-2132000-3	
	C	4.9	3-2132000-2	
	C	4.5	3-2132000-1	
	B	5.5	2-2132000-6	
	B	4.9	2-2132000-5	
	B	4.5	2-2132000-4	
	B	5.5	2-2132000-3	
	B	4.9	2-2132000-2	
	B	4.5	2-2132000-1	
	A	5.5	1-2132000-6	
	A	4.9	1-2132000-5	
	A	4.5	1-2132000-4	
	A	5.5	1-2132000-3	
	A	4.9	1-2132000-2	
	A	4.5	1-2132000-1	
	-	5.5	2132000-6	
	-	4.9	2132000-5	
	-	4.5	2132000-4	
	-	5.5	2132000-3	
	-	4.9	2132000-2	
	-	4.5	2132000-1	OBSOLETE
FINISH	KEY POSITION	DIM M	PART NUMBER	

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

KEY POSITION
CHART

NONE

A

E

B

F

C

G

D

H