





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
G		REVISED PER ECR-24-213594	02JUL2024	RK	FJS




PART NO & DATE CODE MARKED IN AREA INDICATED, ON EITHER SIDE



VIEW B-B
SCALE 10:1
TYPICAL



REAR MOUNTED PANEL CUTOUT
SCALE 1:1



FRONT MOUNTED PANEL CUTOUT
SCALE 1:1

- △ CAVITY IDENTIFICATION CHARACTERS ON FRONT AND REAR FACE.
- △ NYLON, UL 94V-0 RATED, BLACK.
- △ CONTACT BODY: 0.76um [.000030] MIN GOLD FOR A LENGTH OF 2.54 [.100] MIN FROM MATING END, GOLD FLASH ON REMAINDER, BOTH OVER 1.27um [.000050] MIN NICKEL. CONTACT POST: 2.54um [.000100] MIN TIN-LEAD OVER 2.54um [.000100] MIN COPPER.
- △ 5.08um [.000200] MIN NICKEL OVER 10.16um [.000400] MIN COPPER.
- △ CONTACT BODY: 0.76um [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 2.54 [.100] MIN FROM MATING END, GOLD FLASH ON REMAINDER, BOTH OVER 1.27um [.000050] MIN NICKEL. CONTACT POST: 2.54um [.000100] MIN TIN OVER 2.54um [.000100] MIN COPPER.
- △ SELECT LOAD CONTACTS 35 & 36 REMOVED.

OBSOLETE	—	YES	△	41.40 [1.630]	—213597-5—
	△	NO	△	16.38 [.645]	213597-4
OBSOLETE	—	NO	△	16.38 [.645]	—213597-3—
	—	NO	△	16.38 [.645]	—213597-2—
	—	NO	△	14.15 [.557]	—213597-1—
	NOTES	ORGANIZER	CONTACT FINISH	Z	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. SIPE 4-23-90	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK R. STONE 4-25-90			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. DeOLD 4-25-90	NAME		
0 PLC ± -		PRODUCT SPEC	RECEPTACLE ASSEMBLY, 28-37, REVERSE SEX, CMC		
1 PLC ± -		APPLICATION SPEC	108-10040		
2 PLC ± 0.13 [.005]		SIZE	CAGE CODE		
3 PLC ± -		WEIGHT	DRAWING NO		
4 PLC ± -		RESTRICTED TO	A100779		
ANGLES ± -		CUSTOMER DRAWING	SCALE 2:1		
MATERIAL RECEPTACLE: △ SHELL: ZINC CONTACT: BRASS		FINISH SHELL: △	SHEET 1 OF 1		
			REV G		