




REVISIONS 29NOV01 RH						
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	E	REVISED PER ECR-24-213594	02JUL2024	RK	FJS	



RECOMMENDED PANEL CUTOUT




VIEW X-X
TYPICAL
SCALE 10:1

- | | |
|---|--|
| 1 | CAVITY IDENTIFICATION CHARACTERS ON FRONT AND REAR FACE. |
| 2 | .000030 MIN PRECIOUS METAL PLATE FOR A LENGTH OF .250 MIN FROM MATING END OVER .000050 MIN NICKEL. |
| 3 | .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL ON THIS END. |
| 4 | .000100 MIN TIN OVER .000050 MIN NICKEL ON THIS END. |

		.618	213798-3
OBSOLETE		.244	213798-2
OBSOLETE		.618	213798-1
	POST FINISH	DIM L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.BROCKWAY 06-30-94		 TE Connectivity Ltd.			
		CHK R.STONE 07-06-94					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, 23-24, STANDARD SEX, POSTED CONTACTS, CPC			
		APVD —					
		PRODUCT SPEC 108-10024					
		APPLICATION SPEC —					
		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL PIN: BRASS RECEPTACLE: NYLON, BLACK		FINISH —		WEIGHT —		A2 00779 C-213798 —	
CUSTOMER DRAWING				SCALE	SHEET		REV
				2:1	1 OF 2		F

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.BROCKWAY 06-30-94	TE Connectivity Ltd.			
		CHK R.STONE 07-06-94				
DIMENSIONS: INCHES		APVD -	NAME			
		PRODUCT SPEC 108-10024	RECEPTACLE ASSEMBLY, 23-24,STANDARD SEX, POSTED CONTACTS, CPC			
		APPLICATION SPEC -				
MATERIAL PIN: BRASS RECEPTACLE: NYLON, BLACK		FINISH -	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-213798
CUSTOMER DRAWING			SCALE 2:1	SHEET 2 OF 2	REV E	RESTRICTED TO -