




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REVISED PER ECR-24-213594	03JUL2024	RK	FJS



PART NUMBER AND DATE CODE
MARKED ON ANY FLANGE EDGE


- 1 NYLON, UL 94V-0 RATED, BLACK.
- 2 STAINLESS STEEL.
- 3 BRASS.
- 4 CONTACT BODY: .000030 MIN GOLD FOR A LENGTH OF .200 MIN FROM MATING END. GOLD FLASH ON REMAINDER, BOTH OVER .000030 MIN NICKEL.
CONTACT POST: .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL.
- 5 RECOMMENDED PC BOARD HOLE SIZE FOR CONTACT POST = .035±.003 DIA.
- 6 CONTACT BODY: .000030 MIN PRECIOUS METAL PLATE FOR A LENGTH OF .200 MIN FROM MATING END. GOLD FLASH ON REMAINDER, BOTH OVER .000030 MIN NICKEL.
CONTACT POST: .000100 MIN TIN OVER .000050 MIN NICKEL.
- 7 SELECT LOAD: NO CONTACTS LOADED IN POSITIONS 10 AND 32.



OBSOLETE	.490	6	NO	213856-7
		4	NO	213856-6
		6	NO	213856-4
OBSOLETE	.557	4	YES	213856-2
OBSOLETE		4	NO	213856-1
	DIM L	CONTACT FINISH	PERIPHERAL SEAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.HARDY 01-03-95	TE Connectivity Ltd.	
		CHK R.STONE 01-09-95		
DIMENSIONS: INCHES		APVD -	NAME	
		PRODUCT SPEC 108-10024	RECEPTACLE ASSEMBLY, POSTED, REVERSE SEX, 23-37, CPC	
		APPLICATION SPEC 114-10038		
MATERIAL: HOUSING: CONTACT SPRING: CONTACT BODY & POST:		WEIGHT -	SIZE A2	CAGE CODE 00779
FINISH: CONTACT:		DRAWING NO C-213856	RESTRICTED TO -	
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 2
			REV G	

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.HARDY 01-03-95		 TE Connectivity Ltd.			
		CHK R.STONE 01-09-95					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		RECEPTACLE ASSEMBLY, POSTED, REVERSE SEX, 23-37, CPC			
		APVD —				NAME	
		PRODUCT SPEC 108-10024					
		APPLICATION SPEC 114-10038					
0 PLC ± — 1 PLC ± — 2 PLC ± .010 3 PLC ± — 4 PLC ± — ANGLES ± —		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL HOUSING:  CONTACT SPRING:  CONTACT BODY & POST: 		FINISH		WEIGHT —		A2 00779 C-213856	
CONTACT: 		CUSTOMER DRAWING		SCALE 2:1		SHEET 2 OF 2	REV G