


	PER DETAIL Y	PER DETAIL K	K	GRAY	I438894-2	CURRY	1-2138495-0	6-2138894-1
	PER DETAIL Y	PER DETAIL H	H	GRAY	I438894-2	HEATHER VIOLET	2138495-8	5-2138894-8
	PER DETAIL Y	PER DETAIL G	G	GRAY	I438894-2	BLUE GREY	2138495-7	5-2138894-7
	PER DETAIL Y	PER DETAIL F	F	GRAY	I438894-2	NUT BROWN	2138495-6	5-2138894-6
	PER DETAIL Y	PER DETAIL E	E	GRAY	I438894-2	LEAF GREEN	2138495-5	5-2138894-5
	PER DETAIL Y	PER DETAIL D	D	GRAY	I438894-2	CLARET VIOLET	2138495-4	5-2138894-4
	PER DETAIL Y	PER DETAIL C	C	GRAY	I438894-2	SIGNAL BLUE	2138495-3	5-2138894-3
	PER DETAIL Y	PER DETAIL B	B	GRAY	I438894-2	SIGNAL WHITE	2138495-2	5-2138894-2
	PER DETAIL Y	PER DETAIL A	A	GRAY	I438894-2	JET BLACK	2138495-1	5-2138894-1
	PER DETAIL X	PER DETAIL Z	Z	RED	I438888-1	WATER BLUE	2-2138495-1	2-2138894-1
	PER DETAIL X	PER DETAIL M	M	RED	I438888-1	PASTEL ORANGE	1-2138495-2	1-2138894-2
	PER DETAIL X	PER DETAIL K	K	RED	I438888-1	CURRY	1-2138495-0	1-2138894-0
	PER DETAIL X	PER DETAIL H	H	RED	I438888-1	HEATHER VIOLET	2138495-8	2138894-8
	PER DETAIL X	PER DETAIL G	G	RED	I438888-1	BLUE GREY	2138495-7	2138894-7
	PER DETAIL X	PER DETAIL F	F	RED	I438888-1	NUT BROWN	2138495-6	2138894-6
	PER DETAIL X	PER DETAIL E	E	RED	I438888-1	LEAF GREEN	2138495-5	2138894-5
	PER DETAIL X	PER DETAIL D	D	RED	I438888-1	CLARET VIOLET	2138495-4	2138894-4
	PER DETAIL X	PER DETAIL C	C	RED	I438888-1	SIGNAL BLUE	2138495-3	2138894-3
	PER DETAIL X	PER DETAIL B	B	RED	I438888-1	SIGNAL WHITE	2138495-2	2138894-2
	PER DETAIL X	PER DETAIL A	A	RED	I438888-1	JET BLACK	2138495-1	2138894-1
	ASSEMBLY	KEYING	CODING	LOCK COLOR	LOCK PART NUMBER	HOUSING COLOR	PLUG HOUSING PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±0.25
3 PLC ±
4 PLC ±
ANGLES ±°

MATERIAL
FINISH

DWN
K. PETERSON
29DEC2011

CHK
L. VARSIK
29DEC2011

APVD
L. VARSIK
29DEC2011

PRODUCT SPEC
APPLICATION SPEC
114-13157
WEIGHT
CUSTOMER: DRAWING

NAME
PLUG KIT, UNASSEMBLED,
I POSN, MINI 59, RG-58 OR RG-58 LL,
180 DEGREE, FAKRA, SMB


SHEET 1 OF 2

REV A2


SCALE 4:1

RESTRICTED TO


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




DETAIL A
SCALE 5:1




DETAIL B
SCALE 5:1




DETAIL C
SCALE 5:1




DETAIL D
SCALE 5:1




DETAIL E
SCALE 5:1




DETAIL F
SCALE 5:1




DETAIL G
SCALE 5:1




DETAIL H
SCALE 5:1



DETAIL K
SCALE 5:1



DETAIL Z
SCALE 5:1



DETAIL M
SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. PETERSON CHK L. VARSIK APVD L. VARSIK	29DEC2011 29DEC2011 29DEC2011	TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC	
		114-13157		APPLICATION SPEC	
MATERIAL		WEIGHT		SIZE CAGE CODE DRAWING NO	
-		-		A100779C=2138894	
-		CUSTOMER DRAWING		RESTRICTED TO	
		SCALE 4:1		SHEET 2 OF 2	
				REV A2	