



NOTES	FIXED CO Abdeckkappe
Bemerkungen 0-214/1501-1 AS SHOW N 0-214/1501-1 wie gezeichnet	ROTATIVE Drehbare
CAVITY MARKING Kammernummerierung	ADAPTER Adapter für
TE LOGO TE Zeichen	RECEPTAC 1,5 mm Se
ASSEMBLY DATE Zusammenbau Datum	RECEPTAC 1,5 mm Se
PLANT CODE: Herstellungs Land: E = EUROPE C = CHINA M = MERCOSUR	3 WAYS 3 pol. STE
ASST. PKN- AND REVISION FOR EXAMPLE: F-3 F = FORD VERSION; -3 = SUFFIX FOR TE PART NUMBER; R = REVISION Zusammenbau Nr. und Revision Zu Beispiel: F-3/X F = Ford Version; -3 = Nachstrichzahl, fuer TE Teilenummer; X = Revision	



B	E-11-009265	09 JUN 2011
B1	ECR-24-225478	03 SEP 2024
C	OBSELETE : 2141501-6/-4/-9	30 JAN 2025

ACCEPTABLE CABLE SECTIONS PER CONTACT
The cross-section of the cables used must be between 0.5 and 1.5mm² (Ø wire min= 1.40mm; Ø wire Max= 2.40mm) Kabelquerschnitt liegt zwischen 0.5 und 1.5mm² (Ø Min= 1.40mm; Ø Max= 2.40mm)

[illegible]

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN M.Kressmann		30-Jan-25				TE Connectivity		
DIMENSIONS: mm				TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.3 1 PLC ±0.1 2 PLC ±0.3 3 PLC ±0.3 4 PLC ±0.3 ANGLES ±2° FINISH				CMT K.Roth		30SEP2010		
								NAME		3 WAY RECEPTACLE HPST CONNECTOR ASSEMBLY		
				PRODUCT SPEC - APPLICATION SPEC				SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
								A1		00779	C=2141501	
MATERIAL				WEIGHT				CUSTOMER DRAWING				
								SCALE 5:1 SHEET 1 of 1 REV C				