


Die deutsche Version dieser Zeichnung dient nur zur Erleichterung der Handhabung. Bei Abweichungen vom dem englischen Original gilt das englische Original.
The german version of this drawing has been offered for convenience only and may deviate from the english original.
In case of any deviation the English version shall prevail.


Wiedergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz.
Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksausstattung vorbehalten.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.




1)
Sechskantmutter rostfrei ISO 4035 - M4
nut

1) maximales Anzugsmoment: 70 Ncm
max. torque: 70 Ncm


Bausatz in Polybeutel verpackt
kit packed in plastic bag



M 1:1



214362-E	12	6 - 8	144769
214361-E	9,7	2,5 - 6	144768
Ident-Nr. / Id.no.	A	LP-Dicke / board thickness	Stift-Ident-Nr. / pin no.

Dimension no.				Tolerances Dim. for Information ISO 8015		 All Dimensions in mm		Scale 2:1	
<u>Customer drawing:</u> This Drawing is a controlled Document.				Subject to modification without prior notice. Drawing will not be updated.		ERNI-Führungsbolz. vergold. Bausatz ERmet Guiding System			
				 TE Connectivity		C-214379-E		I	
a1		16.03.2023						A3	
Index		Date				Class		ERMBGR	