

1

MATERIAL:
BODY, OUTER CONTACT, RETAINING RING & CENTER CONTACT
BERYLIUM COPPER, ALLOY UNS C17300 CONDITION TDO4, PER ASTM B196.
INSULATOR - TEFLON (PTFE) ROD, PER ASTM D 1710.



2

FINISH:
BODY & CENTER CONTACT - GOLD PLATE, PER ASTM B488
OVER NICKEL PLATE PER, SAE-AMS-QQ-N-290
RETAINING RING - NICKEL PLATE PER, SAE-AMS-QQ-N-290

3

SMPM MALE SMOOTH BORE, PER MIL-STD-348,
EXCEPT AS NOTED.

4. FOR USE WITH ALPEN A24 OR SIMILAR SIZE LOW LOSS CABLE.



2157022-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. T. Morley 07JUL2010	TE Connectivity			
DIMENSIONS: INCHES [mm]		CHK S. T. Morley 07JUL2010				
		APVD S. T. Morley 07JUL2010	NAME SMPM STRAIGHT CABLE PLUG (M) PANEL MOUNT - SOLDER ATTACHMENT FOR USE WITH LOW LOSS CABLE			
		PRODUCT SPEC -	SIZE A2			
MATERIAL 1		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.1 1 PLC ±.01 2 PLC ±.005 3 PLC ±.005 4 PLC ±.005 ANGLES ±. FINISH 2	APPLICATION SPEC 408-10364			
		WEIGHT -	CAGE CODE A200779			
		Customer Drawing	DRAWING NO. C-2157022			
			RESTRICTED TO -			
			SCALE 15:1			
			SHEET 1 OF 1			
			REV A			