



NOTES:

- 1
- CONNECTOR IS DESIGNED FOR FLAT RIBBON CABLE ON 1,27 CENTERS.
FOR CABLE REQUIREMENTS SEE APPLICATION SPECIFICATION 114-19022.
- 2
- INDICATION OF FIRST CABLE POSITION REFERRING TO CORRESPONDING
CONTACT POSITION (BLACK INK MARKS)
- 3
- SOLDER-TINES FOR 0,8^{±0,1} DIA. HOLES.
- 4)
- PRODUCT SPECIFICATION 108-19033
- 5
- OBSOLETE



86,36	78,74	64	6-216093-4	B	5
81,28	73,66	60	6-216093-0	B	5
68,58	60,96	50	5-216093-0	B	5
60,96	53,34	44	4-216093-4	B	5
55,88	48,26	40	4-216093-0	B	
48,26	40,64	34	3-216093-4	B	
38,10	30,48	26	2-216093-6	B	
30,48	22,86	20	2-216093-0	B	
25,40	17,78	16	1-216093-6	B	
22,86	15,24	14	1-216093-4	B	
17,78	10,16	10	1-216093-0	B	
12,70	5,08	6	216093-6 5	B	
DIM. "B" REF.	DIM. "A" REF.	NR. OF POS.	PARTNUMBER	PART REV.	
8	7				

C	REVISED PER ECN-25-325980	MS	JM	09JUN2025	
B4	ECR-10-024640	C.J	R.P	30JUN11	
B3	ECR-10-026537	KK	HMR	19FEB11	
B2	REVISED FOR ET00-0243-04	A. V.	R. M.	21MAR2005	
B1	REVISED PER ET00-0023-04	D. C.	C. T.	09FEB2004	
B	-	-	-	22MAY1989	
LTR.	REVISION RECORD	DR.	CHK.	DATE	

CUSTOMER DRAWING					
FOR REFERENCE ONLY WILL NOT BE UPDATED					
DR. W. R. VERBEET.	DATE 22-8' 88				
CHK. R. VERSTIJNEN.	DATE 23-8' 88				
APP. L. v. SOEST.	DATE 23-8' 88				

③	CONTACTS	PHOSPHORBRONZE	3, 0-5, 1μm TIN WITH ENTIRE NICKEL UNDERCOATING
②	HOUSING AND COVER	THERMOPLASTIC POLYESTER	GREY
①	HOUSING		
COMPONENT NAME		MATERIAL	PLATING / COLOUR
 TE Connectivity			
THIS DRAWING IS UNPUBLISHED		RELEASED FOR PUBLICATION 22-8, 1988	
c COPYRIGHT 1988 BY TE-HOLLAND B. V. ALL INTERNATIONAL RIGHTS RESERVED. TE PRODUCTS MAY BE COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.			
WIRE RANGE SEE NOTE 1		NAME AMP-LATCH 2,54 DIL-PLUG CONNECTOR WITHOUT RETENTION LEGS.	
INSUL. RANGE SEE NOTE 1			
SIZE A3	SHEET 1 OF 1	DWG. No.	REV. LTR.
		C-216093	C