

RELEASED FOR PUBLICATION


ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT copyright date BY -

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	13APR2018	GSK	AP




NOTES:

1. FOR FURTHER INFORMATION SEE DATA SHEET FOR CRGP SERIES SMD PULSE THICK FILM CHIP RESISTORS

RoHS Compliant



SCALE 20:1

DIMENSIONS:		DWN	13APR2018	MATERIAL		FINISH	
mm		GANESH C M		-		-	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	13APR2018	TE Connectivity			
		ALLAN.P					
		APVD	13APR2018				
		ALLAN.P		NAME SMD PULSE THICK FILM CHIP RESISTOR SERIES CRGP 1206			
PRODUCT SPEC		-					
0 PLC ±0.5 1 PLC ±0.2 2 PLC ±0.1 3 PLC ± 4 PLC ± ANGLES ±°		APPLICATION SPEC		SIZE		CAGE CODE	
		-		DRAWING NO		RESTRICTED TO	
		-		A 4		00779	
		WEIGHT		-			
		CUSTOMER DRAWING		SCALE		SHEET	
				30:1		1 OF 1	
						REV A	