






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DS	-		A2	REVISED PER ECR-17-005168	11APR'17	SC	BH




NOTE,
⚠ APPLICABLE PDL REC CONTACT (INSIDE 16 Pos)

WIRE RANGE	PDL CONTACT	FG CONTACT	APPL. SPEC
AWG #26~#22	177914-*	1743728-*	114-5175
AWG #20~#16 2X AWG #24	177915-*	1743729-*	

⚠ APPLICABLE PTL REC CONTACT (OUTSIDE 4 Pos)

WIRE RANGE	CONTACT	APPL. SPEC
AWG #22~#20	1971785-*	114-106118
AWG #19~#16 2X AWG #22	1971783-*	
2X AWG #20~#18	2232499-*	114-61065

3. MATING CAP HSG P/N: 2188646-□
4. MATING TPA HSG P/N: 2188647-2
5. PART MEETS GWT 750°C

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SC KIM 12SEP2016		TE Connectivity											
		CHK BH CHO 12SEP2016													
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± ±0.5 1 PLC ± ± 2 PLC ± ± 3 PLC ± ± 4 PLC ± ± ANGLES ±		NAME PDL/PTL HYB 20P PLUG HSG(2R)											
															
MATERIAL PC/PET (UL94 V-0, CTI 600V)		FINISH -		PRODUCT SPEC 108-61192		APPLICATION SPEC SEE TABLE		SIZE A3		CAGE CODE 00779		DRAWING NO C-2188645		RESTRICTED TO -	
				WEIGHT -		CUSTOMER DRAWING		SCALE 2:1		SHEET 1		OF 1		REV A2	