





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	INITIAL DRAWING	02JAN2019	OL	SZ



*: PLATING ON CONTACT AREA 1: GOLD FLASH 2: 5u" GOLD PLATING 3: 10u" GOLD PLATING 4: 15u" GOLD PLATING 5: 30u" GOLD PLATING 7: 100u" BRIGHT TIN PLATING 8: 100u" MATTE TIN PLATING	39.65	33.00	40.15	24	*-2204812-9
	36.65	30.00	37.15	22	*-2204812-0
	33.65	27.00	34.15	20	9-2204812-*
	30.65	24.00	31.15	18	8-2204812-*
	27.65	21.00	28.15	16	7-2204812-*
	24.65	18.00	25.15	14	6-2204812-*
	21.65	15.00	22.15	12	5-2204812-*
	18.65	12.00	19.15	10	4-2204812-*
	15.65	9.00	16.15	8	3-2204812-*
	12.65	6.00	13.15	6	2-2204812-*
REMARK	9.65	3.00	10.15	4	1-2204812-*
	6.65	N/A	7.15	2	2204812-*
	DIM A	DIM B	DIM C	CIRCUIT	PART NUMBER



NOTES:

1. PART NUMBER AND DATE CODE.
2. MATERIAL:
HOUSING: THERMO PLASTIC, COLOR: BLACK.
TERMINAL: COPPER ALLOY.
3. PLATING: SEE REMARK IN PART NUMBER LIST.

RECOMMENDED PCB LAYOUT (COMPONENT SIDE)
PCB THICKNESS=1.57±0.05MM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ORANDO LI 21DEC2018	TE TE Connectivity PRELIMINARY				
		CHK SUNY ZHAO 21DEC2018					
		APVD SUNY ZHAO 21DEC2018					
		NAME					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		ELCON MICRO POWER CONNECTOR HEADER R/A SMT W/FITTING NAIL 3.00MM PITCH, 2XN CIRCUITS			
		PRODUCT SPEC		RESTRICTED TO			
		108-128068					
		APPLICATION SPEC					
		-					
MATERIAL TBD		FINISH		SIZE	CAGE CODE	DRAWING NO	-
-		-		A3	00779	C-2204812	
		WEIGHT		CUSTOMER DRAWING			
		-		SCALE			
				4:1			
				SHEET			
				1 OF 2			
				REV			
				1			

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20




COPYRIGHT 20

BY -


ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




CIRCUIT SIZE:2




CIRCUIT SIZE:10




CIRCUIT SIZE:18




CIRCUIT SIZE:4




CIRCUIT SIZE:12




CIRCUIT SIZE:20




CIRCUIT SIZE:6




CIRCUIT SIZE:14




CIRCUIT SIZE:22



CIRCUIT SIZE:8



CIRCUIT SIZE:16




CIRCUIT SIZE:24

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.3
2 PLC ±0.2
3 PLC ±-
4 PLC ±-
ANGLES ±-
FINISH -
-

MATERIAL

TBD

-

DWN 21DEC2018

ORANDO LI

CHK 21DEC2018

SUNY ZHAO

APVD 21DEC2018

SUNY ZHAO

PRODUCT SPEC

108-128068

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME
ELCON MICRO POWER CONNECTOR
HEADER R/A SMT W/FITTING NAIL
3.00MM PITCH, 2XN CIRCUITS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779C-2204812

-

SCALE

4:1

SHEET

2

OF

2

REV

1