







- 1 HOUSING: GLASS FILLED NYLON OR POLYESTER, 94V-0 RATED, COLOR - BLACK.
POSTS: PHOSPHOR BRONZE.
- 2 POSTS: $0.76\mu\text{m}$ [.000030] MIN GOLD PLATE ON THE LOCALIZED PLATE AREA, $2.54\mu\text{m}$ [.000100] MIN TIN PLATE ON THE TAIL, $1.27\mu\text{m}$ [.000050] MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
- 3 REFER TO APPLICATION SPECIFICATION 114-40020 FOR HOLE SIZE AND FINISH RECOMMENDATIONS.
- 4 DATUMS M & N TO BE ESTABLISHED BY CUSTOMER.
- 5 NO SLOT FOR SNAP-IN POLARIZER ON THIS END FOR 10 AND 14 POSITION HEADERS.
- 6 NO SLOT ON THIS END FOR 10 POSITION HEADERS.



22.86 [.900]	40.64 [1.600]	44.70 [1.760]	40.64 [1.600]	30.48 [1.200]	20	2214642-4
15.24 [.600]	33.02 [1.300]	37.08 [1.460]	33.02 [1.300]	22.86 [.900]	14	2214642-2
E	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		OWN C. VALENTINE 17FEB2012		 TE Connectivity	
		CHK S. BOLASH 17FEB2012			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HEADER ASSY, UNIVERSAL, ACTION PIN AMP-LATCH	
		0 P.L.C ± - 1 P.L.C ± - 2 P.L.C ± 0.13 [0.005] 3 P.L.C ± - 4 P.L.C ± - ANGLES ± -			
MATERIAL		FINISH		SIZE: CAGE CODE: DRAWING NO. RESTRICTED TO:	
				A1 00779 © 2214642	
		WEIGHT		SCALE: 4:1 SHEET 1 of 1 REV A	
		CUSTOMER DRAWING			