


REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
B1		REVISED (ECR-16-003970)	19.MAY.'16	EW	KT
B2		REVISED (ECR-17-008059)	03.JUL.'17	EW	KT
C		REVISED (ECR-20-001387)	01FEB2020	EW	YJ
C1		REVISED ECR-21-110109	08APR2022	VI	YJ





060/110/250

HYB 38P COVER ASSY TYPE A

PN.2219215-X



SCALE 1:1
<ISO VIEW>




SECTION A-A





060/110/250

HYB 38P COVER ASSY TYPE B

PN.2-2219215-X



SCALE 1:1
<ISO VIEW>



SECTION B-B

NOTES

1. GENERAL TOLERANCE : ± 0.3 , $\pm 3^\circ$
2. DELIVERY CONDITION : CPA IN PRE-LOCKED POSITION
3. APPLICABLE PLUG : X-2219210-X HYB SEALED 38POS PLUG ASSY
4. SEE SHEET 2 OF 2 FOR THE WITHOUT CPA TYPE

NO	COLOR/FINISH	MATERIAL	DESCRIPTION	QT'Y	QT'Y	QT'Y	QT'Y	QT'Y	QT'Y
7	BLACK	PBT	CPA FOR HYB 38POS COVER ASSY	-	1	-	-	-	1
6	RED	PBT	CPA FOR HYB 38POS COVER ASSY	-	-	1	-	-	-
5	GRAY	PBT	CPA FOR HYB 38POS COVER ASSY	1	-	-	1	-	-
4	GRAY	PBT-GF20	HYB 38P COVER HSG TYPE B	-	-	-	-	-	1
3	BLACK	PBT-GF20	HYB 38P COVER HSG TYPE B	-	-	-	-	1	-
2	GRAY	PBT-GF20	HYB 38P COVER HSG TYPE A	-	1	-	-	-	-
1	BLACK	PBT-GF20	HYB 38P COVER HSG TYPE A	1	-	1	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN EW CHUN	TE Connectivity	
			CHK YD LEE		
DIMENSIONS:			APVD KT LIM	NAME	
mm			PRODUCT SPEC	HYB SEALED 38POS COVER ASSEMBLY	
			108-61230		
			APPLICATION SPEC		
MATERIAL			WEIGHT	SIZE	CAGE CODE
SEE TABLE			-	A1	-
			CUSTOMER DRAWING	SCALE	2:1
				SHEET	1
				OF	2
				REV	C1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

060/110/250

HYB 38P COVER W/O CPA "H" TYPE

PN.1-2219215-X

B2











060/110/250

HYB 38P COVER W/O CPA "L" TYPE

PN.3-2219215-2

SCALE 1:1
<ISO VIEW>

SCALE 1:1
<ISO VIEW>



SECTION C-C

SECTION K-K

OBSOLETE	B2	3	BLACK	PBT-GF20	38P COVER HSG W/O CPA "L" TYPE	3-2219215-2
		2	GRAY	PBT-GF20	38P COVER HSG W/O CPA "H" TYPE	1-2219215-3
		1	BLACK	PBT-GF20	38P COVER HSG W/O CPA "H" TYPE	1-2219215-2
		NO	COLOR/FINISH	MATERIAL	DESCRIPTION	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	
DIMENSIONS:				CHK	SEE SHEET 1
mm				APVD	
TOLERANCES UNLESS OTHERWISE SPECIFIED				NAME	
0 PLC				PRODUCT SPEC	
1 PLC				108-61230	
2 PLC				APPLICATION SPEC	
3 PLC				WEIGHT	
4 PLC				CUSTOMER DRAWING	
MATERIAL				SCALE 1:1	
FINISH				SHEET 2 OF 2	
SEE TABLE				REV C1	