





THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
20
COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE	28.AUG.'15	EW	HG
	A1	REVISED (ECR-24-206727)	20MAR2024	KH	KT
	A2	REVISED (ECR-24-220011) SYST. NAME CHANGE	09SEP2024	KH	KT

	2219498-3	29.5
A1	2219498-2	34.5
	PART NO.	DIM "A"±0.5



3D VIEW

SCALE 2:1

NOTES

1. GENERAL TOLERANCE : ±0.3, ±3°

A1	2	GRAY	PBT-GF30	BLIND PLUG FOR MCON-1.2 (S)	2219498-3
	1	BLACK	PA66-GF15	BLIND PLUG FOR MCON-1.2	2219498-2
	NO.	COLOR/FINISH	MATERIAL	DESCRIPTION	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN EW CHUN		TE Connectivity BLIND PLUG FOR MCON-1.2	
DIMENSIONS: mm		CHK KT LIM			
		APVD HG CHO			
		PRODUCT SPEC 108-61265			
MATERIAL SEE TABLE		FINISH /		APPLICATION SPEC -	
		WEIGHT -		RESTRICTED TO	
		CUSTOMER DRAWING		SCALE 4:1	
				SHEET 1 OF 1	
				REV A2	