






NOTE

1. GENERAL TOLRANCE: ± 0.3 , $\pm 2.0^\circ$
2. NO CRACK
3. LASER MARKING. (NO BURNED)
4. THE MATING PLUG ASS'Y P/N:
2219639/2219642/2219645



CUSTOMER DRAWING

MATERIAL

RESTRICTED TO

OF

EV AL

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20


BY -

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1 OF 4			




DRAWING OF 1-2219636-1 (96P HEADER ASSY)



DETAIL X



DETAIL X
SCALE 2:1



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL

-

FINISH

-

DWN

-

CHK

-

APVD

-

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

020 060 106P HEADER ASSY

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-2219636

RESTRICTED TO

-

SCALE

1:1

SHEET

3

OF

4

REV

A1

