




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
C		REV PER ECO 14-013505	9-22-14	CT	WB
D		REVISED PER ECO-17-015513	19DEC2017	PHM	CT



POLARIZATION KEYWAY 3 PLC	ZINC ALLOY PER ASTM-B-86	---
KEYWAY RETAINER PLATE	ALUMINUM ALLOY	BLUE ANODIZED PER MIL-A-8625
150 INSERTS	THERMOPLASTIC	---
SHELL	ALUMINUM ALLOY PER ASTM-B-85	ELECTROLESS NICKEL PER MIL-C-26074 CLASS 4, GRADE B
RETENTION PLATES	ALUMINUM ALLOY PER ASTM-B-209	
COMPONENT	MATERIAL	FINISH

- CONNECTOR MEETS ARINC 600 SPECIFICATIONS
- CONNECTOR IS SUPPLIED WITH A DUST COVER INSTALLED FOR SHIPPING.
- KEYING INSTALLED IN POSITION "01". FOR POSITION "00" KEYING SUPPLIED UNASSEMBLED.
- CONTACTS ARE PACKAGED IN A SEPERATE CONTAINER AND SHIPPED WIYH CONNECTOR.

MODULE A SZ 22 CRIMP SOCKET CONTACT, TE P/N 208264-2 (QTY = 150)	"01"	2221947-1
MODULE B SZ 22 CRIMP SOCKET CONTACT, TE P/N 208264-2 (QTY = 150)		
MODULE C NONE		
CONTACTS INCLUDED AND NOT INSTALLED	KEYING POSITION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS 2-19-14	TE Connectivity
DIMENSIONS: INCHES [mm]		CHK W. BERNHART 2-19-14	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W. BERNHART 2-19-14	
0 PLC ±" 0.005 (0.13)		PRODUCT SPEC	
1 PLC ±" 0.005 (0.13)		APPLICATION SPEC	NAME RECPTACLE ASSY, SIZE 2, ARINC 600 REAR RELEASE, (150/150/DUMMY)
2 PLC ±" 0.005 (0.13)		WEIGHT	
3 PLC ±" 0.005 (0.13)		Customer Drawing	SIZE A1
4 PLC ±" 0.005 (0.13)			CAGE CODE 00779
ANGLES FINISH			DRAWING NO. 2221947
MATERIAL			RESTRICTED TO
			SCALE 3:2
			SHEET 1 OF 1
			REV D