






D




C

B

A



DIMENSION FOR P.C.BOARD (CONNECTOR SIDE)
プリント基板取付寸法 (コネクタ取付面)



1. MATING WITH PLUG HOUSING SMOOTHLY.
PLUG HOUSING PRODUCT NUMBER : 2174106-1
2. TO BE MATED WITH P.C.B OF THICKNESS 1.6mm
3. COMPONENT PART AND CIRCUIT NO. SEE TABLE
4. RECOMMENDED SCREW, 3mm DIA X 8mm LENGTH WITH PAN HEAD CLASS 2 WITH GROOVED (JIS B1122)
TIGHTENING TORQUE : 0.392 N·m (REFERENCE)

1. 相手ハウジングと支障なく嵌合すること
カン合相手型番 ; 2174106-1
2. 厚さ1.6mmのプリント基板に装着できること
3. 構成部品及び回路番号は TABLE 参照
4. 推奨取付けネジ JIS B1122 M3X8ナベ(2種みぞ付き) : 締付けトルク: 0.392N・m (参考)

RETURNABLE PALLET SYSTEM 回収使用/パレット			PAPER BOX ダンボール箱			OUTER 外装	PACKING STYLE 梱包形態	
RETURNABLE TRAY 回収使用トレイ			SOFT BOX プリスタートレイ			INNER 内装		
9	CIRCUIT NO	8~16	9	CIRCUIT NO	8~16	COPPER ALLOY, PRE-TIN	1.0 TAB CONTACT (M)	7
7	CIRCUIT NO	1~7	7	CIRCUIT NO	1~7	COPPER ALLOY, PRE-TIN	1.0 TAB CONTACT (V)	6
10	CIRCUIT NO	41~50	10	CIRCUIT NO	41~50	COPPER ALLOY, PRE-TIN	0.5 TAB CONTACT (S)	5
12	CIRCUIT NO	29~40	12	CIRCUIT NO	29~40	COPPER ALLOY, PRE-TIN	0.5 TAB CONTACT (M)	4
12	CIRCUIT NO	17~28	12	CIRCUIT NO	17~28	COPPER ALLOY, PRE-TIN	0.5 TAB CONTACT (L)	3
1	-	-	1	-	-	PBT, BLACK	TINE PLATE	2
1	-	-	1	-	-	PBT, BLACK	CAP HOUSING	1
QTY	TAB CONTACT POSITION		QTY	TAB CONTACT POSITION		MATERIAL,FINISH/COLOR	NAME	ITEM NO
2229486-2(US)			2229486-1(JPN)			COMPONENT PART		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Y. SUEMITSU CHK Y. NOGUCHI APVD T. KOHNO		10DEC2015 10DEC2015 10DEC2015		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.3		NAME		CAP HOUSING ASSEMBLY 50 POSITION 0.5/1.0 SEALED CONNECTOR	
		0-PLC 1-PLC 2-PLC 3-PLC 4-PLC ANGLES FINISH ± 3°00'		PRODUCT SPEC 108-78947 APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT 28.7 g		RESTRICTED TO	
				A100779C=2229486		-	
CUSTOMER DRAWING		SCALE 2:1		SHEET 1 OF 1		REV A1	