









WIRING TABLE

LOC NO.	PIN NO.	PIN NO.	LOC NO.
CN11	A1	1	CN1,2,3,4,5,6,7,8,9,10
	B1	3	CN1,2,3,4,5,6,7,8,9,10
	A2	2	CN1
	B2	2	CN2
	A3	2	CN3
	B3	2	CN4
	A4	2	CN5
	B4	2	CN6
	A5	2	CN7
	B5	2	CN8
	A6	2	CN9
	B6	2	CN10

1	—	D1200—RITS RELAY 10P BOARD	4
2	1473565—3	RITS HDR 3P 1ROW	3
2	1473567—3	RITS HDR 3P 4ROW	2
1	1—1827875—6	D1200 HDR V 12P	1
QTY	PART NUMBER	NAME	ITEM NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.OSABE 06MAY2013		TE Connectivity	
DIMENSIONS: 単位： 耗 mm		CHK M.HARASAWA 13MAY2015			
		APVD N.YAMASAKI 06MAY2013		NAME 名称 D1200-RITS RELAY BOARD ASSY 10 POINTS TYPE	
		PRODUCT SPEC 製品規格 —			
		APPLICATION SPEC 取付適用規格 —			
MATERIAL 材料 —		WEIGHT 15.2		SIZE CAGE CODE DRAWING NO 番号 A300779C-2229983	RESTRICTED TO —
FINISH 仕上 —		CUSTOMER DRAWING			
				SCALE 尺度 2:1	SHEET 1 OF 1
				REV B	